




Rev	AWO #	Description	Date	Appr
-		RELEASED	10/26/05	
A		ADDED HEIGHT OFF PCB	03/22/06	BAS
B		REVISED SPEC.	1/21/13	

APPROVED: _____

DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT

INSULATOR	TEFLON	NONE
INSULATOR	TEFLON	NONE
PIN	COPPER	TIN
CONTACT PIN	PHOSPHOR	TIN
INSULATOR	TEFLON	NONE
BODY	BRASS	NICKEL
BODY	BRASS	NICKEL
DESCRIPTION	MATERIAL	FINISH

SPECIFICATIONS:

Electrical:

Impedance: 75 ohm

Frequency range: 0–2 GHz

Working Voltage: 250 VRMS max.

Dielectric Withstanding Voltage: 500 VRMS min.

Contact Resistance: 5 Milliohms max. (Center Contact)

2 Milliohms max. (Outer Contact)

Insulator Resistance: 1000 Megohms min.

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
INCHES .X ± .10 .XX ± .020 .XXX ± .015			HOLES ØX ± .10 ØXX ± .015 ØXXX ± .010		
APPROVALS		DATE	TITLE R/A, F TYPE FEMALE, PC MOUNT, 75 OHM TEFLON INSULATOR		
DRAWN	SS	10/26/05	SIZE	PART NO.	REV.
CHECKED			X	RF4-01-T-00-75	B
APPROVED			REF:	SCALE: NTS	SHEET 1 OF 1