


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/15/14	
A		ADDED SPEC.	6/12/14	HR/AY
B		REDRAWN	12/30/14	HR/SL
C		ADDED PIN NUMBER	6/3/16	AY/CH



1 Poles = 2 Screws

Poles	ADAM P/N
1	TDJA-02-V2
2	TDJA-04-V2
3	TDJA-06-V2
4	TDJA-08-V2
5	TDJA-10-V2
6	TDJA-12-V2
7	TDJA-14-V2
8	TDJA-16-V2
9	TDJA-18-V2
10	TDJA-20-V2
11	TDJA-22-V2
12	TDJA-24-V2

SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-2

Insulator color: White

Screws: M4 Steel, Zinc plated

Clamp: Brass, Nickel plated

Electrical:

Voltage rating: 600 V

Current rating: 65 A

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min. @ 500 VDC

Dielectric withstanding voltage: 2,000 VAC for 1 minute

Mechanical:

Wire range: 20-6 AWG, 10 mm²

Strip Length: 7-8 mm

Torque: 1.2 N-m, 10.8 Lb-in

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



A = .575 [14.60] x No. of Poles - .154 [3.90]

B = .575 [14.60] x No. of Spaces

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	HR	5/15/14
CHECKED	SY	5/15/14
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
TERMINAL BLOCK, DUAL ROW, 14.60mm PITCH

SIZE	PART NO.	REV.
X	TDJA-XX-V2	C
REF:	S00067C	SCALE: NTS
SHEET 1 OF 1		