



2400-2500, 5150-7125 MHz Wi-Fi 6E Flat Panel MIMO
Antenna, 6 dBi Gain, 4 RP SMA Male Connectors

Antennas Technical Data Sheet

PEANFP1037

Features

- Reverse Polarity SMA (RP-SMA) Male Connector
- 4 x Vertical Polarization
- 4x4 MIMO Functionality
- Outdoor Rated Flat Panel Antenna
- 2.4 GHz, 5 GHz, 6 GHz Wi-Fi Bands
- 6 dBi gain

Applications

- Infotainment systems, Routers, Wi-Fi hotspots, HD video transmission, Gateways, Dash cameras, Public transportation
- Connected cars or self-driving cars, Fleet management, Logistics
- Public Safety Networks
- Zigbee, Bluetooth, Wi-Fi

Description

The PEANFP1037 Wi-Fi 6e Antenna from Pasternack's is a high performance directional antenna designed for the 2400 MHz to 7125 MHz bands and is available to ship same day. It is a UV protected, outdoor rated antenna with directional pattern. The PEANFP1037 is ideally suited for 802.11 protocols including 802.11ax as well as Zigbee, Bluetooth and is 4x4 MIMO capable.

The Pasternack's high performance PEANFP1037 is a rugged antenna providing broad coverage, low latency, increased network capacity and 6 dBi gain. This 4 port RPSMA Male directional antenna is suitable for commercial radios and access points in public and private networks that are equipped with Reverse Polarity SMA Type connectors.

This Wi-Fi 6e PEANFP1037 antenna with 4 RPSMA Male connectors, as well as our wide selection of superior quality RF parts, ships same day. Contact our knowledgeable and friendly technical support and sales staff for your answers on antennas or other Pasternack's products.

Configuration

Design	Flat Panel
Application Band	Wi-Fi 6E
Band Type	Dual
Radiation Pattern	Directional
Polarization	Vertical
Cable Type	RG58/U
Cable Length	36 in [914.4 mm]
Connector Type	SMA Male Reverse Polarity
Number of Ports	4

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	2,400		7,125	MHz
Input VSWR			2:1	
Impedance		50		Ohms
Input Power			50	Watts

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2400-2500, 5150-7125 MHz Wi-Fi 6E Flat Panel MIMO Antenna, 6 dBi Gain, 4 RP SMA Male Connectors PEANFP1037](#)



2400-2500, 5150-7125 MHz Wi-Fi 6E Flat Panel MIMO
Antenna, 6 dBi Gain, 4 RP SMA Male Connectors

Antennas Technical Data Sheet

PEANFP1037

Specifications by Band

Description	Band 1	Band 2	Band 3	Band 4	Band 5	Units
Range	2.4 to 2.5	5.15 to 7.125				GHz
Gain	6	6				dBi
Horizontal Beam Width	105	120				Degrees
Vertical Beam Width	60	55				Degrees

Mechanical Specifications

Radome Material

UV Resistant ABS

Size

Overall Length

9 in [228.6 mm]

Width

4.4 in [111.76 mm]

Height

1.2 in [30.48 mm]

Weight

2.88 lbs [1.31 kg]

Color

White

Environmental Specifications

Temperature

Operating Range

-40 to +70 deg C

Humidity

5 to 95

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2400-2500, 5150-7125 MHz Wi-Fi 6E Flat Panel MIMO Antenna, 6 dBi Gain, 4 RP SMA Male Connectors PEANFP1037](#)



2400-2500, 5150-7125 MHz Wi-Fi 6E Flat Panel MIMO
Antenna, 6 dBi Gain, 4 RP SMA Male Connectors

Antennas Technical Data Sheet

PEANFP1037

2400-2500, 5150-7125 MHz Wi-Fi 6E Flat Panel MIMO Antenna, 6 dBi Gain, 4 RP SMA Male Connectors from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2400-2500, 5150-7125 MHz Wi-Fi 6E Flat Panel MIMO Antenna, 6 dBi Gain, 4 RP SMA Male Connectors PEANFP1037](https://www.pasternack.com/2400-2500-5150-7125-mhz-wi-fi-6e-flat-panel-mimo-antenna-6-dbi-gain-4-rp-sma-male-connectors-peanfp1037-p.aspx)


URL: <https://www.pasternack.com/2400-2500-5150-7125-mhz-wi-fi-6e-flat-panel-mimo-antenna-6-dbi-gain-4-rp-sma-male-connectors-peanfp1037-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PEANFP1037 CAD Drawing

2400-2500, 5150-7125 MHz Wi-Fi 6E Flat Panel MIMO

Antenna, 6 dBi Gain, 4 RP SMA Male Connectors



NOTES:

1. LABEL PER ILS-100-03 (FOR INTERNAL USE ONLY).
LABEL LOCATION SHOWN IS FOR REFERENCE ONLY.

REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

 PASTERNAK an INFINITI [®] brand		 INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920		SCALE NONE	SHEET 1 OF 1
DESCRIPTION 2400-2500 & 5150-7125MHZ 6DBI WI-FI 6E WIDE BEAMWIDTH SMALL PATCH MIMO ANTENNA, 4 LEADS, POLE MOUNT SMA MALE			
SIZE A	CAGE CODE 53919	DRAWN BY PSRINIVAS	ITEM NO. PEANFP1037
UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE IN INCHES DIMENSIONS IN [] ARE MILLIMETERS		TOLERANCES: X = ±.2 [5] FRACTIONS XX = ±.02 [.5] ± 1/32 XXX = ±.005 [.13] ANGLES ± 1° CABLE LENGTH TOLERANCES: ≤12 [305] = +1 [25] / -0 >12 [305] ≤ 60 [1524] = +2 [51] / -0 >60 [1524] ≤ 120 [3048] = +4 [102] / -0 >120 [3048] ≤ 300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE	