


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/6/15	
A		ADDED PIN NUMBER	5/25/16	AY/SC
B		UPDATE DRAWING	1/4/17	AY/MY



1 Poles = 2 Screws

Poles	ADAM P/N
1	TDJA-02-WP-V2
2	TDJA-04-WP-V2
3	TDJA-06-WP-V2
4	TDJA-08-WP-V2
5	TDJA-10-WP-V2
6	TDJA-12-WP-V2
7	TDJA-14-WP-V2
8	TDJA-16-WP-V2
9	TDJA-18-WP-V2
10	TDJA-20-WP-V2
11	TDJA-22-WP-V2
12	TDJA-24-WP-V2

SPECIFICATIONS:

Material:

Insulator: PA66, rated UL 94V-2

Insulator color: White

Screws: M5 Steel, Zinc plated

Copper Cylinder: Copper Alloy, Nickel plated

Electrical:

Voltage rating: 600 V

Current rating: 65 A

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min. @ 500 VDC

Dielectric withstanding voltage: 2,500 VAC for 1 minute

Mechanical:

Wire range: 12-6 AWG, 16 mm²

Strip Length: 7-8 mm

Torque: 1.5 N-m, 13.0 Lb-in

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



$$A = .575 [14.60] \times \text{No. of Spaces} + .433 [11.00]$$

$$B = .575 [14.60] \times \text{No. of Spaces}$$

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	HR	11/6/15
CHECKED	NC	11/6/15
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
TERMINAL BLOCK, DUAL ROW, 14.60mm PITCH,
WITH WIRE PROTECTOR

SIZE	PART NO.	REV.
X	TDJA-XX-WP-V2	B
REF:	S00067C	SCALE: NTS
SHEET 1 OF 1		