


APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/28/21	
A		UPDATED SPEC.	9/27/21	LH/RC



SPECIFICATIONS:

Material:

Cage: Copper Alloy

Electrometric Gasket: Conductive Rubber

Cage Rear EMI Gasket: Conductive Foam

Front Flange: Zinc Alloy, Tin over Nickel and Copper flash

Front EMI Gasket: Copper Alloy, Matte Tin over Nickel underplate overall

Heat Sink Clip: Copper Alloy

Heat Sink: Aluminum, Anodic Oxidation, Color: Black ▲

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

mm
 .X ± .25
 .XX ± .13
 .XXX ± .10
 Angles
 ± 2°

DRAWN	WX	5/28/21
CHECKED	RC	5/28/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE		REV.	
10 GIGABIT SMALL FORM FACTOR CAGE, 1PORT DIP TYPE, EMI CLIP W/ GASKET, W/ HEAT SINK		A	
SIZE	PART NO.		
X	XFC-1-CS6-EMI-HSK		
REF:	S00005C	SCALE:	NTS
		SHEET	1 OF 2

6

5

4

3

2


1

APPROVED: _____

DATE: _____ TITLE: _____

Rev AWO # Description Date Appr

SEE SHT 1 OF 2 FOR REVISION

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

mm		Angles
.X	$\pm .25$	$\pm 2^\circ$
.XX	$\pm .13$	
.XXX	$\pm .10$	

DRAWN WX 5/28/21

CHECKED RC 5/28/21

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH**ADAM
TECH**909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710TITLE
10 GIGABIT SMALL FORM FACTOR CAGE, 1PORT
DIP TYPE, EMI CLIP W/ GASKET, W/ HEAT SINK

SIZE X PART NO. XFC-1-CS6-EMI-HSK REV. A

REF: S00005C SCALE: NTS SHEET 2 OF 2

6

5

4

3

2

1