

6

5

4

3



2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/28/21	



SPECIFICATIONS:

Material:

Cage: Copper Alloy

Electrometric Gasket: Conductive Rubber

Cage Rear EMI Gasket: Conductive Foam

Front Flange: Zinc Alloy, Nickel Plated

Front EMI Gasket: Copper Alloy, Nickel Plated

Heat Sink Clip: Copper Alloy

Heat Sink: Aluminum, Anodic Oxidation

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

mm	Angles
.X ± .25	± 2°
.XX ± .13	
.XXX ± .10	

DRAWN	WX	5/28/21
CHECKED	RC	5/28/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH
ADAM
TECH





 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

 TITLE
 10 GIGABIT SMALL FORM FACTOR CAGE, 1PORT
 DIP TYPE, EMI CLIP W/ GASKET, W/ HEAT SINK

SIZE X	PART NO. XFC-1-CS7-EMI-HSK	REV. -
REF: S00005C	SCALE: NTS	SHEET 1 OF 2

APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 2 FOR REVISION				



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

mm	Angles
.X $\pm$.25	$\pm 2^\circ$
.XX $\pm$.13	
.XXX $\pm$.10	

DRAWN	WX	5/28/21
CHECKED	RC	5/28/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
10 GIGABIT SMALL FORM FACTOR CAGE, 1PORT
DIP TYPE, EMI CLIP W/ GASKET, W/ HEAT SINK

SIZE X	PART NO. XFC-1-CS7-EMI-HSK	REV. -
REF: S00005C	SCALE: NTS	SHEET 2 OF 2