


Data sheet chainflex® CF880



Control cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket • Flame-retardant



Example image

For detailed overview please see design table

Example image
igus® chainflex® CF880

Cable structure



Conductor

Conductor consisting of bare copper wires (according to DIN EN 60228).



Core insulation

Mechanically high-quality TPE mixture.



Core structure

Cores wound with an optimised pitch length.



Core identification

Black cores with white numbers, one green-yellow core.



Outer jacket

Low-adhesion PVC mixture, adapted to suit the requirements in e-chains®.
Colour: Jet black (similar to RAL 9005)

Printing: white

„00000 m*** igus chainflex M CF880---① ---② 300/500V E310776

cULus AWM Style 2464 VW-1 AWM I/II A/B 80°C 300V FT1 CE

www.igus.de +++ chainflex cable works +++

* Length printing: Not calibrated. Only intended as an orientation aid.

① / ② Cable identification according to Part No. (see technical table).

Example: ... chainflex CF880.15.04 4G1.5 300 V/500 V ...



Data sheet chainflex® CF880



Control cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket • Flame-retardant



Dynamic information



Bend radius

e-chain® linear
flexible
fixed

minimum 12.5 x d
minimum 10 x d
minimum 7 x d



Temperature

e-chain® linear
flexible
fixed

+5°C up to +70°C
-5°C up to +70°C (following DIN EN 60811-504)
-15°C up to +70°C (following DIN EN 50305)



v max.

unsupported

3m/s



a max.

20m/s²



Travel distance

Unsupported travels up to 10m, Class 1



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



These values are based on specific applications or tests. They do not represent the limit of what is technically feasible.

Guaranteed service life according to guarantee conditions

Double strokes	1 million	3 million	5 million
Temperature, from/to [°C]	R min. [x d]	R min. [x d]	R min. [x d]
+5/+15	15	16	17
+15/+60	12.5	13.5	14.5
+60/+70	15	16	17

Minimum guaranteed service life of the cable under the specified conditions.

The installation of the cable is recommended within the middle temperature range.

Electrical information



Nominal voltage

300/500V
300V (following UL)



Testing voltage

2000V (following DIN EN 50395)

Data sheet chainflex® CF880



Control cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket • Flame-retardant



Properties and approvals



Flame-retardant

According to IEC 60332-1-2, Cable Flame, VW-1, FT1, FT2 / Horizontal Flame



Silicone-free

Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)



PTFE-free

The design of these products does not contain PTFE



UL-verified

Certificate No. V293650: „igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year“



UL/CSA AWM

Details see table UL AWM



NFPA

Following NFPA 79-2018, chapter 12.9



REACH

In accordance with regulation (EC) No. 1907/2006 (REACH)




RoHS

Following 2011/65/EC (RoHS-II/RoHS-III)



CE

Following 2014/35/EU



Properties and approvals

UL/CSA AWM Details

Conductor nominal cross section [mm ²]	Number of cores	UL style core insulation	UL style outer jacket	UL Voltage Rating [V]	UL Temperature Rating [°C]
0.5	2-25	10493	2464	300	80
0.75	2-25	10493	2464	300	80
1	2-25	10493	2464	300	80
1.5	2-25	10493	2464	300	80
2.5	3-12	10493	2464	300	80

Data sheet chainflex® CF880




Control cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket • Flame-retardant



Typical lab test setup for this cable series

Test bend radius R	approx. 75 - 225 mm
Test travel S	approx. 1 - 15 m
Test duration	minimum 2 - 4 million double strokes
Test speed	approx. 0.5 - 2 m / s
Test acceleration	approx. 0.5 - 1.5 m / s ²



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Example image

Data sheet chainflex® CF880



Control cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket • Flame-retardant

Technical tables:

Mechanical information

Part No.	Number of cores and conductor nominal cross section [mm ²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF880.05.02	2x0.5	5.0	11	32
CF880.05.03	3G0.5	5.5	16	37
CF880.05.04	4G0.5	6.0	21	46
CF880.05.05	5G0.5	6.5	26	55
CF880.05.07	7G0.5	7.5	37	73
CF880.05.12	12G0.5	8.5	63	108
CF880.05.18	18G0.5	10.0	94	158
CF880.05.25	25G0.5	12.0	128	227
CF880.07.02	2x0.75	5.5	16	40
CF880.07.03	3G0.75	6.0	24	49
CF880.07.04	4G0.75	6.5	32	61
CF880.07.05	5G0.75	7.0	40	73
CF880.07.07	7G0.75	8.0	56	99
CF880.07.12	12G0.75	10.0	94	152
CF880.07.18	18G0.75	11.5	140	167
CF880.07.25	25G0.75	13.5	194	284
CF880.10.02	2x1.0	6.0	21	48
CF880.10.03	3G1.0	6.5	32	58
CF880.10.04	4G1.0	7.0	42	62
CF880.10.05	5G1.0	7.5	52	86
CF880.10.07	7G1.0	8.5	73	116
CF880.10.12	12G1.0	10.5	124	182
CF880.10.18	18G1.0	12.5	186	278
CF880.10.25	25G1.0	15.0	258	393
CF880.15.02	2x1.5	6.5	32	64
CF880.15.03	3G1.5	7.0	47	82
CF880.15.04	4G1.5	7.5	63	104
CF880.15.05	5G1.5	8.5	78	120
CF880.15.07	7G1.5	10.0	109	167
CF880.15.12	12G1.5	12.0	186	260
CF880.15.18	18G1.5	14.5	279	370
CF880.15.25	25G1.5	17.5	387	514

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.

G = with green-yellow earth core X = without earth core



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year



Example image



igus® chainflex® CF880

Data sheet

chainflex® CF880



Control cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket • Flame-retardant



igus® chainflex® CF880

Part No.	Number of cores and conductor nominal cross section [mm ²]	Outer diameter (d) max. [mm]	Copper index [kg/km]	Weight [kg/km]
CF880.25.03	3G2.5	8.5	78	120
CF880.25.04	4G2.5	9.0	103	150
CF880.25.05	5G2.5	10.0	129	184
CF880.25.07	7G2.5	12.0	181	256
CF880.25.12	12G2.5	15.0	327	414

Note: The given outer diameters are maximum values and may tend toward lower tolerance limits.

G = with green-yellow earth core X = without earth core



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year

Electrical information

Conductor nominal cross section [mm ²]	Maximum conductor resistance at 20 °C (following DIN EN 50289-1-2) [Ω/km]	Max. current rating at 30 °C [A]
0.5	39	10
0.75	26	13
1	19.5	15
1.5	13.3	19
2.5	8	27

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.



Data sheet chainflex® CF880



Control cable (Class 3.1.1.1) • For flexing applications • PVC outer jacket • Flame-retardant



Design table

Part No.	Number of cores	Core design	Part No.	Number of cores	Core design
CF880.XX.02	2		CF880.XX.07	7	
CF880.XX.03	3		CF880.XX.12	12	
CF880.XX.04	4		CF880.XX.18	18	
CF880.XX.05	5		CF880.XX.25	25	

Example image

igus® chainflex® CF880



igus 4-year
chainflex cable
guarantee and
service life
calculator based
on 2 billion test
cycles per year

