


# Data sheet chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant  
• Flame-retardant



1. Outer jacket: Pressure extruded iguPUR mixture
2. Core insulation: Mechanically high-quality TPE mixture
3. Conductor: Stranded conductor consisting of bare copper wires
4. Filling: Plastic yarns



## Example image

For detailed overview please see design table

## Cable structure



### Conductor

Conductor consisting of bare copper wires (according to DIN EN 60228).



### Core insulation

Mechanically high-quality TPE mixture.



### Core structure

Cores wound with an optimised pitch length.



### Core identification

Black cores with white numbers, one green-yellow core.



### Outer jacket

Low-adhesion iguPUR mixture, adapted to suit the requirements in e-chains®.

Colour: Jet black (similar to RAL 9005)

Printing: white



„00000 m\*\*\* igus chainflex M CF890---① ---② 300/500V E310776

cULus AWM Style 20940 VW-1 AWM I/II A/B 80°C 600V FT1 EAC CE UKCA

RoHS-II conform [www.igus.de](http://www.igus.de) +++ chainflex cable works +++

\* Length printing: Not calibrated. Only intended as an orientation aid.

① / ② Cable identification according to Part No. (see technical table).

Example: ... chainflex CF890.15.04 4G1.5 300 V/500 V ...

# Data sheet chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant  
● Flame-retardant



## Dynamic information



Bend radius

e-chain® linear  
flexible  
fixed

minimum 12.5 x d  
minimum 10 x d  
minimum 7 x d



Temperature

e-chain® linear  
flexible  
fixed

-20°C up to +80°C  
-40°C up to +80°C (following DIN EN 60811-504)  
-50°C up to +80°C (following DIN EN 50305)



v max.

unsupported

3m/s



a max.

20m/s<sup>2</sup>



Travel distance

Unsupported travels up to 10m, Class 1



These values are based on specific applications or tests. They do not represent the limit of what is technically feasible.

## Guaranteed service life according to guarantee conditions

| Double strokes            | 1 million    | 3 million    | 5 million    |
|---------------------------|--------------|--------------|--------------|
| Temperature, from/to [°C] | R min. [x d] | R min. [x d] | R min. [x d] |
| -20/-10                   | 15           | 16           | 17           |
| -10/+70                   | 12.5         | 13.5         | 14.5         |
| +70/+80                   | 15           | 16           | 17           |

Minimum guaranteed service life of the cable under the specified conditions.

The installation of the cable is recommended within the middle temperature range.

## Electrical information



Nominal voltage

300/500V  
600V (following UL)



Testing voltage

2000V (following DIN EN 50395)

# Data sheet chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant  
• Flame-retardant



## Properties and approvals



UV resistance

Medium



Oil resistance

Oil-resistant (following DIN EN 50363-10-2), Class 3



Flame-retardant

According to IEC 60332-1-2, Cable Flame, VW-1, FT1, FT2 / Horizontal Flame



Silicone-free

Free from silicone which can affect paint adhesion (following PV 3.10.7 – status 1992)



PTFE-free

The design of these products does not contain PTFE



UL-verified

Certificate No. V293650: „igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year“



UL/CSA AWM

Details see table UL/CSA AWM



NFPA

Following NFPA 79-2018, chapter 12.9



REACH

In accordance with regulation (EC) No. 1907/2006 (REACH)



RoHS

Following 2011/65/EC (RoHS-II/RoHS-III)



CE

Following 2014/35/EU



## Properties and approvals

### UL/CSA AWM Details

| Conductor nominal cross section<br>[mm <sup>2</sup> ] | Number of cores | UL style core insulation | UL style outer jacket | UL Voltage Rating<br>[V] | UL Temperature Rating<br>[°C] |
|---|-----------------|--------------------------|-----------------------|--------------------------|-------------------------------|
| 0.5   | 2-25            | 11323                    | 20940                 | 600                      | 80                            |
| 0.75  | 2-25            | 11323                    | 20940                 | 600                      | 80                            |
| 1   | 2-25            | 11323                    | 20940                 | 600                      | 80                            |
| 1.5   | 2-25            | 11323                    | 20940                 | 600                      | 80                            |
| 2.5   | 3-25            | 11323                    | 20940                 | 600                      | 80                            |

Example image

igus® chainflex® CF890

# Data sheet chainflex® CF890




Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant  
● Flame-retardant



## Typical lab test setup for this cable series

|                    |                                      |
|--------------------|--------------------------------------|
| Test bend radius R | approx. 75 - 225 mm                  |
| Test travel S      | approx. 1 - 15 m                     |
| Test duration      | minimum 2 - 4 million double strokes |
| Test speed         | approx. 0.5 - 2 m / s                |
| Test acceleration  | approx. 0.5 - 1.5 m / s <sup>2</sup> |



igus 4-year  
chainflex cable  
guarantee and  
service life  
calculator based  
on 2 billion test  
cycles per year



## Typical application areas

- For flexing applications, Class 3
- Especially for unsupported travels, Class 1
- With influence of oil, Class 3
- No torsion, Class 1
- Indoor and outdoor applications without direct sun radiation
- Machining units/machine tools, low temperature applications

Example image

igus® chainflex® CF890

# Data sheet chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant  
• Flame-retardant



## Technical tables:

### Mechanical information

| Part No.    | Number of cores and conductor nominal cross section<br>[mm <sup>2</sup> ] | Outer diameter (d) max.<br>[mm] | Copper index<br>[kg/km] | Weight<br>[kg/km] |
|-------------|---|---------------------------------|-------------------------|-------------------|
| CF890.05.02 | 2x0.5   | 5.0                             | 11                      | 30                |
| CF890.05.03 | 3G0.5   | 5.5                             | 16                      | 34                |
| CF890.05.04 | 4G0.5   | 6.0                             | 21                      | 44                |
| CF890.05.05 | 5G0.5   | 6.5                             | 26                      | 53                |
| CF890.05.07 | 7G0.5   | 7.5                             | 37                      | 70                |
| CF890.05.12 | 12G0.5  | 8.5                             | 63                      | 105               |
| CF890.05.18 | 18G0.5  | 10.0                            | 94                      | 155               |
| CF890.05.25 | 25G0.5  | 12.0                            | 128                     | 222               |
| CF890.07.02 | 2x0.75  | 5.5                             | 16                      | 38                |
| CF890.07.03 | 3G0.75  | 6.0                             | 24                      | 46                |
| CF890.07.04 | 4G0.75  | 6.5                             | 32                      | 58                |
| CF890.07.05 | 5G0.75  | 7.0                             | 40                      | 71                |
| CF890.07.07 | 7G0.75  | 8.0                             | 56                      | 96                |
| CF890.07.12 | 12G0.75   | 10.0                            | 94                      | 146               |
| CF890.07.18 | 18G0.75   | 11.5                            | 140                     | 162               |
| CF890.07.25 | 25G0.75   | 13.5                            | 194                     | 278               |
| CF890.10.02 | 2x1.0   | 6.0                             | 21                      | 46                |
| CF890.10.03 | 3G1.0   | 6.5                             | 32                      | 56                |
| CF890.10.04 | 4G1.0   | 7.0                             | 42                      | 58                |
| CF890.10.05 | 5G1.0   | 7.5                             | 52                      | 89                |
| CF890.10.07 | 7G1.0   | 8.5                             | 73                      | 117               |
| CF890.10.12 | 12G1.0  | 10.5                            | 124                     | 178               |
| CF890.10.18 | 18G1.0  | 12.5                            | 186                     | 273               |
| CF890.10.25 | 25G1.0  | 15.0                            | 258                     | 375               |
| CF890.15.02 | 2x1.5   | 6.5                             | 32                      | 62                |
| CF890.15.03 | 3G1.5   | 7.0                             | 47                      | 76                |
| CF890.15.04 | 4G1.5   | 7.5                             | 63                      | 97                |
| CF890.15.05 | 5G1.5   | 8.5                             | 78                      | 117               |
| CF890.15.07 | 7G1.5   | 10.0                            | 109                     | 163               |
| CF890.15.12 | 12G1.5  | 12.0                            | 186                     | 256               |
| CF890.15.18 | 18G1.5  | 14.5                            | 279                     | 362               |
| CF890.15.25 | 25G1.5  | 17.5                            | 387                     | 502               |

**Note:** The given outer diameters are maximum values and may tend toward lower tolerance limits.  
**G** = with green-yellow earth core **x** = without earth core



igus 4-year  
chainflex cable  
guarantee and  
service life  
calculator based  
on 2 billion test  
cycles per year



# Data sheet chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant  
• Flame-retardant



## Technical tables:

### Mechanical information

| Part No.    | Number of cores and conductor nominal cross section<br>[mm <sup>2</sup> ] | Outer diameter (d) max.<br>[mm] | Copper index<br>[kg/km] | Weight<br>[kg/km] |
|-------------|---|---------------------------------|-------------------------|-------------------|
| CF890.25.03 | 3G2.5   | 8.5                             | 78                      | 136               |
| CF890.25.04 | 4G2.5   | 9.0                             | 103                     | 145               |
| CF890.25.05 | 5G2.5   | 10.0                            | 129                     | 175               |
| CF890.25.07 | 7G2.5   | 12.0                            | 181                     | 246               |
| CF890.25.12 | 12G2.5  | 15.0                            | 327                     | 408               |
| CF890.25.25 | 25G2.5  | 21.5                            | 638                     | 786               |

**Note:** The given outer diameters are maximum values and may tend toward lower tolerance limits.

G = with green-yellow earth core X = without earth core



igus 4-year  
chainflex cable  
guarantee and  
service life  
calculator based  
on 2 billion test  
cycles per year



### Electrical information

| Conductor nominal cross section<br>[mm <sup>2</sup> ] | Maximum conductor resistance at 20 °C<br>(following DIN EN 50289-1-2)<br>[Ω/km] | Max. current rating at 30 °C<br>[A] |
|---|---|-------------------------------------|
| 0.5   | 39  | 10                                  |
| 0.75  | 26  | 14                                  |
| 1   | 19.5  | 17                                  |
| 1.5   | 13.3  | 21                                  |
| 2.5   | 8   | 30                                  |

The final maximum current rating depends among other things on the ambient conditions, the type of the installation and the number of loaded cores.

# Data sheet chainflex® CF890



Control cable (Class 3.1.3.1) • For flexing applications • iguPUR outer jacket • Oil-resistant  
• Flame-retardant

## Design table

| Part No.    | Number of cores | Core design | Part No.    | Number of cores | Core design |
|-------------|-----------------|-------------|-------------|-----------------|-------------|
| CF890.XX.02 | 2               |             | CF890.XX.07 | 7               |             |
| CF890.XX.03 | 3               |             | CF890.XX.12 | 12              |             |
| CF890.XX.04 | 4               |             | CF890.XX.18 | 18              |             |
| CF890.XX.05 | 5               |             | CF890.XX.25 | 25              |             |



igus 4-year chainflex cable guarantee and service life calculator based on 2 billion test cycles per year



Example image



igus® chainflex® CF890