



Representative Image

Alternate Catalog No. S802S-C20

Catalog No. 2CCS862001R0204

Description: MCB S800S 2P C 20A

UPC No 7612271200633

Home > Circuit Breakers > Miniature Circuit Breakers > Supplementary Protectors

The S802S-C20 is a 2-pole High Performance Circuit breaker with C-characteristic, with cage terminal and a rated current of 20 A. It is a current limiting device with a maximum breaking capacity of 50kA at 240/415V. It can be used for voltages up to 400/690V and in DC as well. It has two different tripping mechanisms, the thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. The S802S-C20 complies with IEC/EN 60898-1 and IEC/EN 60947-2 and allows the use for residential, commercial and industrial applications. It has numerous of approvals, therefore it can be used worldwide. The extensive range of accessory makes the use of S802S-C20 more comfortable. Due to the fast arc extinction of S802S-C20 your application will be secured.

Descriptors

Category

Supplementary Protectors

Specifications

Number of Poles	2
Tripping Characteristic	C
Rated Current	20 A
Standards	IEC/EN 60947-2 IEC/EN 60898-1 UL 1077
Product Main Type	S800S
Rated Voltage (V)	(240 V AC) (480Y / 277 V AC) (600Y / 347 V AC) (240 V AC) 30 kA (480Y / 277 V AC) 14 kA (600Y / 347 V AC) 6 kA
Interrupting Rating acc. to UL1077	(230 / 400 V AC) 25 kA
Rated Short-Circuit Capacity	(240 / 415 V AC) 50 kA (254 / 440 V AC) 30 kA (400 / 690 V AC) 6 kA (125 V DC) 30 kA
Power Loss	at Rated Operating Conditions per Pole 3.5 W