



Representative Image

## Alternate Catalog No. AF116-40-22-11 Catalog No. 1SFL427101R1122

**Description:** AF116-40-22-11 Contactor

**UPC No** 7320500504000

**Home > Contactors & Starters > UL Listed IEC Contactors > AF Contactors**

A 3-phase Contactor suitable for various applications such as Motor starting, Isolation, By-pass and Distribution application up to max 690 V. Operated with wide control voltage range 24-60 V, 50 and 60 Hz, 20-60 V DC

### Descriptors

|                      |                  |
|----------------------|------------------|
| Category             | AF Contactors    |
| Block Contactor Type | 4-Pole Contactor |

### Specifications

|                                                    |                                                                                                                                                                                                                        |
|----------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Type                                       | AF                                                                                                                                                                                                                     |
| General Use Rating UL/CSA                          | (600 V AC) 160 A                                                                                                                                                                                                       |
| Object Classification Code                         | Q                                                                                                                                                                                                                      |
| Terminal Type                                      | Double Clamp                                                                                                                                                                                                           |
| Rated Control Circuit Voltage                      | 50 Hz /60 Hz 24 ... 60 V<br>DC Operation 20 ... 60 V                                                                                                                                                                   |
| Number of Main Contacts NO                         | 4                                                                                                                                                                                                                      |
| Number of Main Contacts NC                         | 0                                                                                                                                                                                                                      |
| Maximum Operating Voltage UL/CSA                   | Main Circuit 600 V                                                                                                                                                                                                     |
| Number of Auxiliary Contacts NO                    | 2                                                                                                                                                                                                                      |
| RoHS Status                                        | Following EU Directive 2011/65/EU                                                                                                                                                                                      |
| Reference Ambient Air Temperature                  | Close to Contactor for Storage -40 ... +70 °C<br>Close to Contactor Fitted with Thermal O/L Relay (0.85 ... 1.1 Uc)<br>-25 ... +50 °C<br>Close to Contactor without Thermal O/L Relay (0.85 ... 1.1 Uc) -40 ... +70 °C |
| Rated Operational Voltage                          | Main Circuit 690 V                                                                                                                                                                                                     |
| Number of Auxiliary Contacts NC                    | 2                                                                                                                                                                                                                      |
| Maximum Operating Altitude Permissible             | 3000 m                                                                                                                                                                                                                 |
| Rated Operational Current AC-1                     | (690 V) 40 °C 160 A<br>(690 V) 60 °C 145 A<br>(690 V) 70 °C 130 A                                                                                                                                                      |
| Rated Operational Power AC-3                       | (220 / 230 / 240 V) 30 KWT<br>(380 / 400 V) 55 KWT<br>(415 V) 55 KWT<br>(440 V) 75 KWT                                                                                                                                 |
| Rated Breaking Capacity AC-3 acc. to IEC 60947-4-1 | 8 x Ie AC-3                                                                                                                                                                                                            |
| Conventional Free-air Thermal Current              | acc. to IEC 60947-4-1, Open Contactors q = 40 °C 160 A                                                                                                                                                                 |
| Rated Frequency                                    | Main Circuit 60 Hz                                                                                                                                                                                                     |

**by ABB**

## Specifications

|                                                  |                                                                                                                                                                                                                                                                                                                                                                                      |
|--------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Rated Short-time Withstand Current               | at 40 °C Ambient Temp, in Free Air, from a Cold State 10 s 928 A<br>at 40 °C Ambient Temp, in Free Air, from a Cold State 15 min 160 A<br>at 40 °C Ambient Temp, in Free Air, from a Cold State 1 min 379 A<br>at 40 °C Ambient Temp, in Free Air, from a Cold State 1 s 1300 A<br>at 40 °C Ambient Temp, in Free Air, from a Cold State 30 s 536 A                                  |
| Rated Operational Current AC-3                   | (220 / 230 / 240 V) 55 °C 116 A<br>(380 / 400 V) 55 °C 116 A<br>(415 V) 55 °C 116 A<br>(440 V) 55 °C 116 A                                                                                                                                                                                                                                                                           |
| Rated Making Capacity AC-3 acc. to IEC 60947-4-1 | 10 x I <sub>e</sub> AC-3                                                                                                                                                                                                                                                                                                                                                             |
| Maximum Electrical Switching Frequency           | AC-1 300 cycles per hour                                                                                                                                                                                                                                                                                                                                                             |
| Short-Circuit Protective Devices                 | gG Type Fuses 200 A                                                                                                                                                                                                                                                                                                                                                                  |
| Rated Insulation Voltage                         | acc. to UL/CSA 600 V<br>acc. to IEC 60947-4-1 and VDE 0110 (Gr. C) 1000 V                                                                                                                                                                                                                                                                                                            |
| Maximum Breaking Capacity                        | cos phi=0.45 (cos phi=0.35 for I <sub>e</sub> > 100 A) at 440 V 2000 A                                                                                                                                                                                                                                                                                                               |
| Mechanical Durability                            | 5 million                                                                                                                                                                                                                                                                                                                                                                            |
| Coil Operating Limits                            | (acc. to IEC 60947-4-1) 0.85 x U <sub>c</sub> Min. ... 1.1 x U <sub>c</sub> Max. (at θ ≤ 70 °C)                                                                                                                                                                                                                                                                                      |
| Maximum Mechanical Switching Frequency           | 300 cycles per hour                                                                                                                                                                                                                                                                                                                                                                  |
| Operate Time                                     | Between Coil De-energization and NO Contact Opening 40 ... 70 ms<br>Between Coil Energization and NO Contact Closing 20 ... 55 ms                                                                                                                                                                                                                                                    |
| Secondary Rated Impulse Withstand Voltage        | Main Circuit 8 kV                                                                                                                                                                                                                                                                                                                                                                    |
| Connecting Capacity Main Circuit                 | Flexible 2 x 10 ... 70 m <sup>2</sup><br>Rigid Cu-Cable 2 x 10 ... 95 m <sup>2</sup>                                                                                                                                                                                                                                                                                                 |
| Coil Consumption                                 | Holding at Max. Rated Control Circuit Voltage 50 Hz 5.5 V - A<br>Holding at Max. Rated Control Circuit Voltage 60 Hz 5.5 V - A<br>Holding at Max. Rated Control Circuit Voltage DC 2.5 W<br>Pull-in at Max. Rated Control Circuit Voltage 50 Hz 225 V - A<br>Pull-in at Max. Rated Control Circuit Voltage 60 Hz 225 V - A<br>Pull-in at Max. Rated Control Circuit Voltage DC 210 W |
| Degree of Protection                             | acc. to IEC 60529, IEC 60947-1, EN 60529 Coil Terminals IP20<br>acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP00                                                                                                                                                                                                                                                         |
| Connecting Capacity Auxiliary Circuit            | Flexible with Ferrule 1 x 0.75 ... 2.5 m <sup>2</sup><br>Flexible 2x0.75 ... 2.5 m <sup>2</sup><br>Solid 1 x 1 ... 4 m <sup>2</sup><br>Stranded 2 x 1 .... 4 m <sup>2</sup>                                                                                                                                                                                                          |

## Classifications

|                                    |                                           |
|------------------------------------|-------------------------------------------|
| ETIM 4                             | EC000066 - Magnet contactor, AC-switching |
| ETIM 6.0                           | EC000066 - Power contactor, AC switching  |
| ETIM 7                             | EC000066 - Power contactor, AC switching  |
| IDEA Granular Category Code (IGCC) | 4755 >> Contactors                        |
| ETIM 5.0                           | EC000066 - Magnet contactor, AC-switching |

## Dimensions

|                            |         |
|----------------------------|---------|
| Product Net Weight         | 2.05 kg |
| Product Net Depth / Length | 128 mm  |
| Product Net Width          | 120 mm  |
| Product Net Height         | 150 mm  |

## Package Information

|                                |               |
|--------------------------------|---------------|
| Package Level 1 Width          | 147 mm        |
| Package Level 1 Height         | 155 mm        |
| Package Level 1 Depth / Length | 197 mm        |
| Package Level 1 EAN            | 7320500504000 |

### Package Information

|                              |             |
|------------------------------|-------------|
| Package Level 1 Units        | box 1 piece |
| Package Level 1 Gross Weight | 2.25 kg     |

### Ordering

|                        |          |
|------------------------|----------|
| Minimum Order Quantity | 1        |
| Customs Tariff Number  | 85364900 |