

Inductive Proximity Sensor, cylindrical, M12 threaded, non-shielded, Ni-Cu alloy, NPN NO, sensing distance 8mm, 2m 3-wire cable



PXINDTLN12-08NO

Inductive Proximity Sensor

Features

- Fast response
- Corrosion resistant housings
- Immunity to wet and/or dusty conditions
- Short-circuit protection
- IP67 protection

Applications

- Industrial Automation
- Automotive
- Materials production
- Warehouse automation
- Food & Beverage

Description

The L-com PXINDTLN12-08NO is a proximity sensor, which is used in countless IoT and industrial automation applications. This inductive proximity IOT sensor is designed in a cylindrical shape and is suitable for the materials production, warehouse automation, automotive, food, and beverage industries. Our IP67 sensor has a sensing distance of 8.00 mm, which allows users to count, inspect objects, and detect their presence and position without physical contact. This proximity sensor is made of corrosion resistant nickel copper alloy and has a tough IP67 housing.

General Specifications

| | |
|--------------------|---------------------------------------|
| Design Type | Cylindrical |
| Output Type | NPN |
| Sensing Distance | 8 mm |
| Supply Voltage | 10-30 VDC |
| Repeat Accuracy | 5 % |
| Hysteresis | 15 % |
| IP Rating | IP67 |
| Housing Material | Nickel Copper Alloy |
| Housing Size | M12 |
| Protective Circuit | Short Circuit |
| Connection Method | 2M 3-wire Cable |
| Leakage Current | 0.01 mA |
| Load Current | 150 mA |
| Voltage Drop | 2 V |
| Mounting | With M12 nuts, tightening torque 16Nm |

(For more information please consult User Manual)

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
Inductive Proximity Sensor, cylindrical, M12 threaded, non-shielded, Ni-Cu alloy, NPN NO, sensing distance 8mm, 2m 3-wire cable PXINDTLN12-08NO

Inductive Proximity Sensor, cylindrical, M12 threaded, non-shielded, Ni-Cu alloy, NPN NO, sensing distance 8mm, 2m 3-wire cable




PXINDTLN12-08NO

Inductive Proximity Sensor

Circuit Diagram

DC 3-Wire

NPN Output



Environmental Specifications

Temperature

Operating Range


-25 to +75 deg C

Inductive Proximity Sensor, cylindrical, M12 threaded, non-shielded, Ni-Cu alloy, NPN NO, sensing distance 8mm, 2m 3-wire cable from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Inductive Proximity Sensor, cylindrical, M12 threaded, non-shielded, Ni-Cu alloy, NPN NO, sensing distance 8mm, 2m 3-wire cable

L-com CAD Drawing



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE
WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

T-Rev-D