



Representative Image

## Catalog No. 696-41794

**Description:** CABLE TIE 0.5IN 1000FT REEL ACETAL

**UPC No** 786210070391

**Home > Wire & Cable Management > Deltec > Cable ties**

Deltec Cable Tie Without Double-Locking Head, Black Acetal for Temperatures up to 105 Degrees Celsius (221 F), Weather and Ultraviolet Resistant, Length of 304.8m (1000 Foot) Reel, Width of 12.7mm (0.5 Inch), Thickness of 1.52mm (0.06 Inch), Tensile Strength Rating of 1112 Newtons (250 Pounds), Can Be Cut to Any Desired Length, Special Pack

### Descriptors

Category	Cable ties
Special Features	Perfect for coaxial, fiber optic and all other communication and electrical conducting cables.
Application	Ideal solution for bundling in harsh outdoor environments.

### Specifications

Material	Weather Resistant Acetal
Color	Black
Lock Mechanism	Double Locking Head
Tensile Strength	250 pounds , 1112 newtons

### Classifications

Brand Name	Deltec
------------	--------

### Dimensions

Width	0.5 in , 12.7 mm
-------	------------------

### Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 233 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	12.7 mm
Length belt/tape/tie	304.8 mm
Length belt/tape/tie	12 inch
Tie thickness	1.52 mm
Tie thickness	0.06 inch

**by ABB**

ETIM	EC000046 Cable tie
Min. holding force	1112 N
Operation temperature	-40-+105 °C
Operation temperature	-40-+221 °F
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Polyoxymethylene (POM)
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	N