



Representative Image

Catalog No. A71M

Description: NON-INS RING TERM 22-16 1/4 MYLAR

UPC No 786210859255

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Non-Insulated Ring Terminal, Length .92 Inches, Width .50 Inches, Bolt Hole 1/4 Inch, Wire Range #22-#16 AWG, Copper, Tin Plated, On Mylar Tape, 1,000 Pack

Descriptors

Category	Electrical terminals
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Application	Wiring terminations or connections for applications such as wiring harness, panelboard, telecommunications, and automotive.

Specifications

Voltage Rating	600 V
Material	Copper
Color	Metallic

Classifications

Brand Name	Sta-Kon
Standard	UL E9809 UL E9809

Dimensions

Wire Size	22-16 AWG
-----------	-----------

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	Y
AWG-range	22-16
Material	Copper
Surface protection	Tinned
Stud size (imperial)	1/4 inch