



**Catalog No. L-8-120-0-C**

**Description: UV NYLON**

**UPC No 728494917405**

**Home > Wire & Cable Management > Catamount > Cable ties**

Cable Tie, Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Length of 200mm (7.87 Inches), Width of 7.6mm (0.30 Inches), Thickness of 1.6mm (0.06 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds)

**Descriptors**

Category	Cable ties
----------	------------

**Specifications**

Material	Nylon/Polyamide 6.6 Weather Resistant
Color	Black
Lock Mechanism	Plastic Pawl
Tensile Strength	120 pounds , 534 newtons

**Classifications**

Brand Name	Catamount
Standard	UL E49405 UL E49405

**Dimensions**

Width	0.3 in , 7.6 mm
Length	8.35 in , 212 mm
Thickness	0.08 in , 2 mm
Bundle Diameter	0.28 to 1.97 in , 7 to 50 mm

**Compliance and Certifications**

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC000046 Cable tie
Band width	7.6 mm
Length belt/tape/tie	212 mm
Length belt/tape/tie	8.35 inch

**by ABB**

ETIM	EC000046 Cable tie
Tie thickness	2 mm
Tie thickness	0.08 inch
Max. bundle diameter	50 mm
Min. holding force	534 N
Operation temperature	-40-+85 °C
Operation temperature	-40-+185 °F
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide (PA)
Surface protection	Untreated
Halogen free	Y
Colour	Black
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y
Inflammability class of insulation material acc. with UL94	V2