



CAT. No.	A	B	C	D	E	F	G "NPT" THREAD
LH210	2.87 (73)	2.64 (67)	4.53 (115)	2.28 (58)	1.89 (48)	1.69 (43)	1/2
LH216-H	3.68 (93.5)	3.46 (88)	5.34 (135.5)	2.28 (58)	2.99 (76)	1.69 (43)	3/4
LH316-H	3.68 (93.5)	3.46 (88)	5.34 (135.5)	2.28 (58)	2.99 (76)	1.69 (43)	1
LH224	4.72 (120)	3.94 (100)	6.38 (162)	2.28 (58)	2.95 (75)	1.69 (43)	3/4
LH324	4.72 (120)	3.94 (100)	6.38 (162)	2.28 (58)	2.95 (75)	1.69 (43)	1
LH232A	3.23 (82)	4.41 (112)	4.92 (125)	2.72 (69)	2.99 (76)	1.69 (43)	3/4
LH332A	3.23 (82)	4.41 (112)	4.92 (125)	2.72 (69)	2.99 (76)	1.69 (43)	1
LH216MV	3.7 (94)		5.4 (137)	2.2 (56)	3.2 (81.5)	1.77 (45)	3/4

NOTES:

1. MATERIAL:  
HOUSING - DIE CAST ALUMINUM WITH EPOXY COAT FINISH  
LEVERS - STEEL WITH ZINC & CHROME PLATING

2. ENVIRONMENTAL RATING: IP65 WHEN MATED & LOCKED

3. UL RECOGNIZED AND CSA CERTIFIED

4. DIMENSIONS ARE IN INCHES (MILLIMETERS).

GENERAL NOTES		DESCRIPTION: <b>LATCHING HOODS TOP ENTRY WITH DOUBLE LEVERS</b>			<b>Thomas&amp;Betts</b> www.tnb.com	
REVISIONS						
** SEE ERN ( **** ) FOR APPROVAL SIGNATURES & RELEASE DATE. PROJECT NO: ****		ORIGINAL PROJECT NO / ( ERN NO )			REV. NO:	DRAWING NO: <b>WSD-000604</b>
TM400024 / ( 2012527 )			1 OF 1	<b>0</b>		