



**Main**

Range of Product	9007
Series name	Severe duty
Product or Component Type	Limit switch lever
Device short name	9007T/FT
Associated head	9007AS9 9007NS9 9007CS9 9007T10S9 9007BS9 9007T5S9
Associated complete product	9007FT 9007T 9007C..S9
Movement of operating head	Rotary
Type of operator	Cast zinc spring return roller lever 5 in (127.00 mm) - convertible roller
Type of roller	1 steel outside roller (convertible) 0.75 in (19.05 mm) 0.25 in (6.35 mm)
Type of approach	Lateral approach
Positive opening	Without

**Complementary**

Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

**Environment**

Ambient Air Temperature for Operation	-10...185 °F (-23...85 °C)
Ambient Air Temperature for Storage	-10...185 °F (-23...85 °C)
Environmental characteristic	Standard environment

**Ordering and shipping details**

Category	21494-9007 ARMS FOR FT,T
Discount Schedule	DS1
GTIN	785901887935
Returnability	Yes
Country of origin	MX

**Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	4.02 in (10.2 cm)
Package 1 Length	7.99 in (20.3 cm)
Package 1 Weight	3.52 oz (99.8 g)
Unit Type of Package 2	S01
Number of Units in Package 2	25
Package 2 Height	5.91 in (15.0 cm)

Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	6.01 lb(US) (2.725 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------