

Product availability: Non-Stock - Not normally stocked in distribution facility  
Important message: We have updated the process to order Telemecanique Sensors products. For more information, please contact your Telemecanique Sensors representative at ([US.salesorders@tesensors.com](mailto:US.salesorders@tesensors.com)). You can find all product information on the Telemecanique Sensors website: <https://tesensors.com/us/en>



### Commercial status

This Product is Obsolete : SEP 01, 2023

⚠ This Product is Obsolete

### Main

|                    |                                 |
|--------------------|---------------------------------|
| Device short name  | C                               |
| Head type          | Type C turret head rotary lever |
| Provided equipment | Receptacle                      |
| Series name        | Heavy duty                      |

### Complementary

|                               |                                    |
|-------------------------------|------------------------------------|
| Line Rated Current            | 10 A                               |
| Body Material                 | Zinc alloy                         |
| Cable entry                   | 0.5 In (12.7 mm) NPT conduit entry |
| Contact code designation      | A600<br>R300                       |
| Contact form                  | Form ZZ DPDT-DB                    |
| Contacts material             | Silver alloy (Ag/Ni)               |
| Contact operation             | Snap action                        |
| Contacts type and composition | 2 NO/2 NC                          |
| Maximum displacement angle    | 90 °                               |
| Pilot light                   | Without pilot lamp                 |
| Switch actuation              | CW and CCW                         |
| Tilting angle                 | 45 °                               |
| Torque Value                  | 3 Lbf.In (0.3 N.m)                 |

### Environment

|                                       |                                |
|---------------------------------------|--------------------------------|
| Ambient Air Temperature for Operation | -20...185 °F (-29...85 °C)     |
| Environmental characteristic          | Hazardous location             |
| Product Certifications                | UL Listed[RETURN]CE[RETURN]CSA |

## Ordering and shipping details

|                   |              |
|-------------------|--------------|
| Category          | US10DS121499 |
| Discount Schedule | 0DS1         |
| Returnability     | No           |

## Packing Units

|                        |                         |
|------------------------|-------------------------|
| Unit Type of Package 1 | PCE                     |
| Nbr. of units in pkg.  | 1                       |
| Package 1 Height       | 6.985 In (17.742 cm)    |
| Package 1 Width        | 2.750 In (6.985 cm)     |
| Package 1 Length       | 17.742 In (45.064 cm)   |
| Package weight(Lbs)    | 2.500 Lb(US) (1.134 kg) |

## Environmental data

|                                        |                                                                                                                                 |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| Sustainable packaging                  | No                                                                                                                              |
| Environmental Disclosure               |  <a href="#">Product Environmental Profile</a> |
| Packaging made with recycled cardboard | No                                                                                                                              |
| Packaging without single use plastic   | No                                                                                                                              |
| California proposition 65              | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is                              |
| Circularity Profile                    | No need of specific recycling operations                                                                                        |
| Take-back                              | No                                                                                                                              |

|                                                      |
|------------------------------------------------------|
| Product Life Status : <b>End of commerc. - Block</b> |
|------------------------------------------------------|