

Product data sheet

Characteristics

9007R21

Limit switch lever, 9007, arm t+ft+options



Main

| | |
|-----------------------------|--|
| Range of Product | 9007 |
| Series name | Severe duty |
| Product or Component Type | Limit switch lever |
| Device short name | 9007T/FT |
| Associated head | 9007BS9 9007T10S9 9007T5S9 9007CS9 9007AS9 9007NS9 |
| Associated complete product | 9007FT 9007T 9007C..S9 |
| Movement of operating head | Rotary |
| Type of operator | Cast zinc vertical roller lever 8.44 in (214.38 mm) - conveyor roller and shaft without clamp (use 9007R16 or 17) |
| Type of roller | 1 acetal resin conveyor side guide roller 1.5 in (38.10 mm) 3.75 in (95.25 mm) |
| Type of approach | Lateral approach |
| Positive opening | Without |

Complementary

| | |
|------------------|----------------------|
| Switch actuation | By conveyor belt |
| Net Weight | 0.1 lb(US) (0.05 kg) |

Environment

| | |
|---------------------------------------|----------------------------|
| Ambient Air Temperature for Operation | -10...185 °F (-23...85 °C) |
| Ambient Air Temperature for Storage | -10...185 °F (-23...85 °C) |
| Environmental characteristic | Standard environment |

Ordering and shipping details

| | |
|-------------------|--------------------------|
| Category | 21494-9007 ARMS FOR FT,T |
| Discount Schedule | DS1 |
| GTIN | 785901910930 |
| Returnability | Yes |
| Country of origin | MX |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 21.59 in (54.839 cm) |
| Package 1 Width | 8.50 in (21.59 cm) |
| Package 1 Length | 54.84 in (139.29 cm) |
| Package 1 Weight | 9.92 oz (281.227 g) |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation |  REACH Declaration |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| Environmental Disclosure |  Product Environmental Profile |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|