

# Product data sheet

## Characteristics

# 9049HF3

## Float, 9049, switch accessory stainless steel 304



### Main

Range of Product	9049
Product or Component Type	Float

### Complementary

Product Compatibility	9037H 9038D 9038C
Type of float	Float tapped at top stainless steel 304
Diameter	2.5 in (63.50 mm)
Length	7 in (177.80 mm)
Product Weight	0.95 lb(US) (0.43 kg)

### Ordering and shipping details

Category	21617-9049 ACCESSORIES (DISCOUNT CP7G)
Discount Schedule	CP7G
GTIN	785901522973
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.16 in (25.806 cm)
Package 1 Width	4.00 in (10.16 cm)
Package 1 Length	25.81 in (65.548 cm)
Package 1 Weight	15.20 oz (430.913 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	20
Package 2 Height	10.00 in (25.4 cm)
Package 2 Width	12.80 in (32.512 cm)
Package 2 Length	15.20 in (38.608 cm)
Package 2 Weight	19.09 lb(US) (8.659 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>
Circularity Profile	 <a href="#">End Of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------