



**Main**

Range of Product	L100/300
Series name	Severe duty
Product or Component Type	Limit switch lever
Device short name	L100/300
Associated complete product	HML300 L100 HML100 L300 ML100 HL300 HL100 ML300
Movement of operating head	Rotary
Type of operator	Aluminium spring return adjustable roller lever 2... 4 in (50.80...101.60 mm) - -
Type of roller	1 steel outside roller 0.75 in (19.05 mm) 0.25 in (6.35 mm)
Type of approach	Lateral approach
Positive opening	Without

**Complementary**

Switch actuation	By 30° cam
Net Weight	0.1 lb(US) (0.05 kg)

**Environment**

Ambient Air Temperature for Operation	-10...185 °F (-23...85 °C)
Ambient Air Temperature for Storage	-10...185 °F (-23...85 °C)
Environmental characteristic	Standard environment

**Ordering and shipping details**

Category	21519-9007 MISCELLANEOUS
Discount Schedule	DS1
GTIN	785901096702
Returnability	No
Country of origin	MX

**Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.30 in (13.462 cm)
Package 1 Width	7.00 in (17.78 cm)
Package 1 Length	7.60 in (19.304 cm)
Package 1 Weight	1.60 oz (45.359 g)

## Offer Sustainability

California proposition 65

WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

REACH Regulation

 [REACH Declaration](#)

EU RoHS Directive

Not applicable, out of EU RoHS legal scope

Environmental Disclosure

 [Product Environmental Profile](#)

## Contractual warranty

Warranty

18 months