

Product availability: Non-Stock - Not normally stocked in distribution facility

**Main**

Base plate style	Style C
Device application	Standard mill switch Universal mill switch Heavy duty
Device short name	T
Series name	Severe duty

**Complementary**

[I <sub>th</sub> ] conventional free air thermal current	20 A
[U <sub>i</sub> ] rated insulation voltage	600 V
AWG gauge	AWG 22...AWG 12
Body material	Cast zinc
Cable entry	0.5 in NPT conduit entry
Contact code designation	A600 P600
Contacts material	Silver flashed copper
Contact operation	Snap action
Maximum displacement angle	90 °
Positive opening	Without
Stage of operation	Contactor closed
Switch actuation	CW and CCW
Tilting angle	45 °
Torque value	8 lbf.in
Tripping angle	0 °

**Environment**

Ambient air temperature for operation	-10...185 °F
Electrical shock protection class	Class 0
IP degree of protection	IP65 IP66 IP67
NEMA degree of protection	NEMA 1/2/4/12/13
Product certifications	CE CSA UL listed
Protective treatment	Corrosion resistant gray paint
Shock resistance	30 gn

**Ordering and shipping details**

Category	21497 - 9007 FT,T OILTIGHT AND FOUNDRY
Discount Schedule	DS1
GTIN	00785901808961
Nbr. of units in pkg.	1
Package weight(Lbs)	2.5

Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------