

Product data sheet

Characteristics

TCSMCN1M1F2

Radio frequency identification XG, Modbus shielded cable, M12 male connector, M12 female connector, IP67, 2 m



Main

| | |
|---------------------------------------|-------------------------------------------------|
| Range of Product | Telemecanique Radio frequency identification XG |
| Accessory / separate part category | Connection accessories |
| Accessory / Separate Part Type | Connecting cable |
| Accessory / separate part designation | Modbus shielded connecting cable |
| Accessory / separate part destination | Compact station Tap-off box |
| Cable length | 6.56 ft (2 m) |

Complementary

| | |
|-----------------------|------------------------------------------------------------------------------------|
| Electrical connection | 1 female connector M12 straight A coding 1 male connector M12 straight A coding |
| Color | Black |
| Net Weight | 0.25 lb(US) (0.115 kg) |

Environment

| | |
|-------------------------|------|
| IP Degree of Protection | IP67 |
|-------------------------|------|

Ordering and shipping details

| | |
|-------------------|----------------------------------|
| Category | 22490-SENSORS-ULTRASONIC (XX5,6) |
| Discount Schedule | DS2 |
| GTIN | 3389119018463 |
| Returnability | No |
| Country of origin | PL |

Packing Units

| | |
|------------------------------|------------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 0.79 in (2.0 cm) |
| Package 1 Width | 7.48 in (19.0 cm) |
| Package 1 Length | 7.68 in (19.5 cm) |
| Package 1 Weight | 5.36 oz (152.0 g) |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 16 |
| Package 2 Height | 5.91 in (15.0 cm) |
| Package 2 Width | 11.81 in (30.0 cm) |
| Package 2 Length | 15.75 in (40.0 cm) |
| Package 2 Weight | 6.27 lb(US) (2.844 kg) |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation |  REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information |  Yes |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|