

Product data sheet

Characteristics

XCRZ04

Limit switch lever, Limit switches XC Standard, XCRZ, steel square rod 6 mm, L=300 mm



Main

Range of Product	OsiSense XC
Series name	Special format
Product or Component Type	Limit switch lever
Device short name	XCRZ
Product Compatibility	XCRA XCRB
Movement of operating head	Rotary
Type of operator	Square rod metal square rod 6 mm, L = 300 mm
Switch actuation	By any moving part
Type of approach	Lateral approach
Positive opening	With

Complementary

Associated complete product	XCRB11 XCRB52 XCRB15 XCRA15 XCRA11 XCRB55 XCRA12 XCRA51 XCRA55 XCRA52 XCRB12 XCRB51
Net Weight	0.06 lb(US) (0.029 kg)

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
---------------------------------------	----------------------------

Ordering and shipping details

Category	18407-WORLD SERVICE PARTS(SENSORS)
Discount Schedule	T
GTIN	3389110652420
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.28 in (0.7 cm)
Package 1 Width	0.28 in (0.7 cm)
Package 1 Length	11.81 in (30 cm)
Package 1 Weight	1.23 oz (35 g)
Unit Type of Package 2	S02
Number of Units in Package 2	100
Package 2 Height	5.91 in (15 cm)

Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	8.34 lb(US) (3.784 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------