

Low PIM 7/16 DIN Male to 7/16 DIN Male Plenum
Cable SPP-250-LLPL Coax in 100 CM




FMCA1305-100CM

Configuration

- Connector 1: 7/16 DIN Male
- Connector 2: 7/16 DIN Male
- Cable Type: SPP-250-LLPL
- Coax Flex Type: Corrugated

Features

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 100 dB
- 76% Phase Velocity
- FEP Jacket
- Low PIM < -160 dBc
- IP67 (Mated)
- Low Loss with Excellent VSWR
- PIM Test Results Marked on Each Cable
- UL910 Plenum Rated Cable
- Extremely Flexible and Lightweight



Applications

- General Purpose
- Laboratory Use
- Low PIM Applications
- DAS
- Mobile Networks
- In-Building Wireless
- Small Cells
- PIM Testing

Description

Low PIM 7/16 DIN male to 7/16 DIN male in 100cm part number FMCA1305-100CM from Fairview Microwave is in-stock and ships same day. This low PIM 7/16 DIN male to 7/16 DIN male in 100cm plenum coax cable assembly offers low PIM performance to support Distributed Antenna Systems (DAS), in-building wireless and other emerging mobile communication networks. The SPP-250-LLPL coax cable carries a UL910 rating for plenum installations. Each low PIM 7/16 DIN male to 7/16 DIN male in 100cm cable assembly is marked with its actual Passive Intermodulation (PIM) test result.

Fairview's FMCA1305-100CM datasheet specifications and outline drawing are shown below in this PDF. Our extensive offering of low PIM cable assemblies, low-PIM adapters and other RF products support multi-carrier system prototype, cable installations and PIM testing applications.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.35:1	
Velocity of Propagation		76		%
RF Shielding	100			dB
Passive Intermodulation		-165	-160	dBc
IM3 (2x43dBm Tones) at 850 MHz or 1900 MHz				

Low PIM 7/16 DIN Male to 7/16 DIN Male Plenum
Cable SPP-250-LLPL Coax in 100 CM



FMCA1305-100CM

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Capacitance		26.7 [87.6]		pF/ft [pF/m]
Operating Voltage (AC)			750	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2	4	6	GHz
Insertion Loss (Max.)	0.53	0.58	0.67	0.8	0.9	dB
VSWR (Max.)	1.25:1	1.25:1	1.25:1	1.35:1	1.35:1	
Power Handling (Max.)	850	507	460	370	250	Watts

Electrical Specification Notes:

Values at 25°C, sea level

PIM test results vary between cables

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. The Insertion Loss includes an estimated loss of 0.4dB of connector loss.

Mechanical Specifications

Cable Assembly

Width/Diameter 0.28 in [7.11 mm]
Weight 0.567 lbs [257.19 g]

Cable

Cable Type SPP-250-LLPL
Inner Conductor Type Solid
Inner Conductor Material and Plating Copper, Bare
Dielectric Type PTFE
Number of Shields 1
Shield Layer 1 Annular Corrugated Copper Tube
Outer Conductor Diameter 0.25 in [6.35 mm]
Jacket Material FEP
Jacket Diameter 0.28 in [7.11 mm]
One Time Minimum Bend Radius 1.5 in [38.1 mm]

Low PIM 7/16 DIN Male to 7/16 DIN Male Plenum
Cable SPP-250-LLPL Coax in 100 CM



FMCA1305-100CM

Connectors

Description	Connector 1	Connector 2
Type	7/16 DIN Male	7/16 DIN Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Silver	Brass, Silver
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Seal Gasket Material	Silicone Rubber	Silicone Rubber

Environmental Specifications

Operating Range Temperature	-55 to +125 deg C
Plenum Rating	UL910

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

Low PIM 7/16 DIN Male to 7/16 DIN Male Plenum
Cable SPP-250-LLPL Coax in 100 CM



FMCA1305-100CM

Typical Performance Data




Low PIM 7/16 DIN Male to 7/16 DIN Male Plenum
Cable SPP-250-LLPL Coax in 100 CM



FMCA1305-100CM

How to Order

Part Number Configuration:



Example: FMCA1305-12 = 12 inches long cable
FMCA1305-100cm = 100 cm long cable

Low PIM 7/16 DIN Male to 7/16 DIN Male Plenum Cable SPP-250-LLPL Coax in 100 CM from Fairview Microwave is in-stock and available to ship same-day. All of our RF/microwave products are available off-the-shelf from our ISO 9001:2008 certified facilities in Lewisville, Texas. Fairview Microwave is RF on-demand.

For additional information on this product, please click the following link: [Low PIM 7/16 DIN Male to 7/16 DIN Male Plenum Cable SPP-250-LLPL Coax in 100 CM FMCA1305-100CM](https://www.fairviewmicrowave.com/low-pim-7-16-din-male-7-16-din-male-cable-spp250llpl-coax-fmca1305-100cm-p.aspx)

URL: <https://www.fairviewmicrowave.com/low-pim-7-16-din-male-7-16-din-male-cable-spp250llpl-coax-fmca1305-100cm-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Fairview Microwave reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Fairview Microwave does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Fairview Microwave does not assume liability arising out of the use of any part or document.

FMCA1305-100CM CAD Drawing

Low PIM 7/16 DIN Male to 7/16 DIN Male Plenum Cable SPP-250-LLPL Coax in 100 CM

