

# Product data sheet

## Characteristics

# ZCKE23

Limit switch head, Limit switches XC Standard, ZCKE, steel roller lever plunger



### Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product Compatibility	XCKJ
Associated body	ZCKJ7H7 ZCKJD37H7 ZCKJD31 ZCKJ11 ZCKJ21H29 ZCKJ6H29 ZCKJD39H29 ZCKJ21 ZCKJ5 ZCKJD39 ZCKJ8H29 ZCKJD31H7 ZCKJ2H7 ZCKJ9H29 ZCKJ6 ZCKJ5H7 ZCKJ7 ZCKJD37H29 ZCKJ2 ZCKJ41 ZCKJ1 ZCKJ11H29 ZCKJ7H29 ZCKJD35H7 ZCKJ6H7 ZCKJ8 ZCKJD35 ZCKJ1H29 ZCKJ5H29 ZCKJ9H7 ZCKJ4H7 ZCKJ11H7 ZCKJ4H29 ZCKJD35H29 ZCKJ41H29 ZCKJD31H29 ZCKJD39H7 ZCKJD37 ZCKJ8H7 ZCKJ41H7 ZCKJ21H7 ZCKJ4 ZCKJ1H7 ZCKJ2H29 ZCKJ9
Movement of operating head	Linear Rotary
Type of operator	Roller lever plunger spring return metal
Type of approach	Lateral approach, 1 direction

### Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

## Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

## Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110646221
Returnability	Yes
Country of origin	US

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.44 in (6.2 cm)
Package 1 Width	2.83 in (7.2 cm)
Package 1 Length	3.70 in (9.4 cm)
Package 1 Weight	6.84 oz (194 g)
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	10.78 lb(US) (4.889 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisobutyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes
Environmental Disclosure	 <a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------