CUI Devices is now Same Sky! Learn More

SERIES: PBM11 | DESCRIPTION: PUSH BUTTON SWITCH

FEATURES

- stainless steel
- 22 mm
- IP67
- illuminated



SPECIFICATIONS

parameter	conditions/description	min	typ	max	units
rated voltage				36 250	Vdc Vac
rated current	Vdc Vac			2.0 5.0	A A
withstanding voltage	for 1 minute		1,000		Vac
contact resistance				50	mΩ
insulation resistance	at 500 Vdc	100			MΩ
operating force		400	600	800	gf
actuator travel		2.3	2.8	3.3	mm
operating temperature		-25		70	°C
life	electrical mechanical		20,000 200,000		cycles cycles
hand soldering	for 3±0.5 seconds	345	350	355	°C
RoHS	yes				
IP level	IP67				

LED SPECIFICATIONS

parameter	conditions/description	min	typ	max	units
forward voltage (Vf)	at I_F=15 mA				
	red (2 V)	1.8	2.0	2.4	V
	yellow (2 V)	1.8	2.0	2.4	V
	blue (3 V)	2.8	3.0	3.4	V
	green (3 V)	2.8	3.0	3.4	V
	white (3 V)	2.8	3.0	3.4	V
	blue (12 V)	5.0	12	13.0	V
	green (12 V)	5.0	12	13.0	V
	red (12 V)	5.0	12	13.0	V
	white (12 V)	5.0	12	13.0	V
	yellow (12V)	5.0	12	13.0	V

PART NUMBER KEY

PBM11 - M - XXX - XX - SS - 67


Base Number

LED Color/Voltage:
R2 = red, 2 V
YL2 = yellow, 2 V
BL3 = blue, 3 V
GR3 = green, 3 V
WT3 = white, 3 V
BL12 = blue, 12 V
GR12 = green, 12 V
R12 = red, 12 V
WT12 = white, 12 V
YL12 = yellow, 12 V


Button Type:
F = flush
P-F = flush, with power emblem
R = raised


MECHANICAL DRAWING (FLUSH, ILLUMINATED)


units: mm
tolerance:
X≤5.0: ±0.2 mm
5.0<X<30.0: ±0.5 mm
X≥30.0: ±1.0 mm
unless otherwise noted
panel thickness: 10.0 mm max




DESCRIPTION	MATERIAL	PLATING/COLOR
housing	stainless steel	---
actuator	stainless steel	---
switch terminals	brass	gold
LED terminals	brass	silver
nut	brass	nickel
base	PA66 (UL94HB)	blue & red









ACTUATOR POSITION (): MOMENTARY	
NORMAL	DOWN
OFF	[ON]
SCHEMATIC	








Recommended Panel Cutout


LED Table	
Model	2~12 V LED
Polarity	


MECHANICAL DRAWING (FLUSH, ILLUMINATED WITH POWER EMBLEM)


units: mm
tolerance:
X≤5.0: ±0.2 mm
5.0<X<30.0: ±0.5 mm
X≥30.0: ±1.0 mm
unless otherwise noted
panel thickness: 10.0 mm max




DESCRIPTION	MATERIAL	PLATING/COLOR
housing	stainless steel	---
actuator	stainless steel	---
switch terminals	brass	gold
LED terminals	brass	silver
nut	brass	nickel
base	PA66 (UL94HB)	blue & red









ACTUATOR POSITION (): MOMENTARY	
NORMAL	DOWN
OFF	[ON]
SCHEMATIC	








Recommended Panel Cutout


LED Table	
Model	2~12 V LED
Polarity	


MECHANICAL DRAWING (RAISED, ILLUMINATED)


units: mm
tolerance:
X≤5.0: ±0.2 mm
5.0<X<30.0: ±0.3 mm
X≥30.0: ±0.5 mm
unless otherwise noted
panel thickness: 10.0 mm max




DESCRIPTION	MATERIAL	PLATING/COLOR
housing	stainless steel	---
actuator	stainless steel	---
switch terminals	brass	gold
LED terminals	brass	silver
nut	brass	nickel
base	PA66 (UL94HB)	blue & red










ACTUATOR POSITION (): MOMENTARY	
NORMAL	DOWN
OFF	[ON]
SCHEMATIC	







Recommended Panel Cutout

LED Table	
Model	2~12 V LED
Polarity	

REVISION HISTORY

rev.	description	date
1.0	initial release	09/02/2026

The revision history provided is for informational purposes only and is believed to be accurate.

same sky

Same Sky offers a one (1) year limited warranty. Complete warranty information is listed on our website.

Same Sky reserves the right to make changes to the product at any time without notice. Information provided by Same Sky is believed to be accurate and reliable. However, no responsibility is assumed by Same Sky for its use, nor for any infringements of patents or other rights of third parties which may result from its use.

Same Sky products are not authorized or warranted for use as critical components in equipment that requires an extremely high level of reliability. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

sameskydevices.com