


Annular SH Series Thermoelectric Cooler


The SH10-95-06-L-RT-W12 is an annular-style thermoelectric cooler. The hot and cold side ceramics have a circular hole in the center to accommodate light protrusion for optics, mechanical fastening or temperature probe. It has a maximum Q_c of 19.1 Watts when $\Delta T = 0$ and a maximum ΔT of 70.5 °C at $Q_c = 0$.

**Features**

- Center Hole
- Precise Temperature Control
- No sound or vibration
- Reliable solid-state
- DC Operation
- RoHS-compliant

Applications

- Thermoelectric Coolers for Reagent Storage
- Thermoelectric Coolers for Handheld Cosmetic Lasers
- Cooling for Centrifuges
- Peltier Cooling for Machine Vision

CERAMIC MATERIAL: Al_2O_3




SOLDER CONSTRUCTION: 138°C, BiSn

INCHES [MM]


Note: Allow 0.020 in [0.5 mm] around perimeter of the thermoelectric cooler and lead wire attachment to accommodate sealant

Electrical and Thermal Performance


For maximum performance, be sure to orient the CONTROL side of the TEC against the application to be managed and the AMBIENT side against the heat sink or other heat rejection method. The CONTROL side is always opposite the side with lead attachments. Lead attachment is a passive heat loss and less impactful if located on the side that attaches to the heat exchanger.

Heat Pumped at Cold Side
 $T_{\text{hot}} = 27^\circ\text{C}$ Heat Pumped at Cold Side
 $T_{\text{hot}} = 27^\circ\text{C}$ Current vs Voltage (I vs V)
 $T_{\text{hot}} = 27^\circ\text{C}$ 


Coefficient of Performance (COP = Q_c/P_{in})
 $T_{hot} = 27^\circ C$




Coefficient of Performance (COP = Q_c/P_{in})
 $T_{hot} = 27^\circ C$




Total Heat Dissipated at Hot Side ($Q_h = Q_c + P_{in}$)
 $T_{hot} = 27^\circ C$




Total Heat Dissipated at Hot Side ($Q_h = Q_c + P_{in}$)
 $T_{hot} = 27^\circ C$



Heat Pumped at Cold Side (Q_c)
 $T_{hot} = 35^\circ C$ | $I_{operating} = 2.6$ Amps



Coefficient of Performance (COP = Q_c/P_{in})
 $T_{hot} = 35^\circ C$ | $I_{operating} = 2.6$ Amps



Specifications

| Hot Side Temperature | 27.0 °C | 35.0 °C | 50.0 °C |
|--|-------------|------------|------------|
| Qcmax ($\Delta T = 0$) | 19.1 Watts | 19.6 Watts | 20.7 Watts |
| ΔT_{max} ($Q_c = 0$) | 70.5°C | 73.5°C | 78.8°C |
| I _{max} (I @ ΔT_{max}) | 3.1 Amps | 3.1 Amps | 3.0 Amps |
| V _{max} (V @ ΔT_{max}) | 10.4 Volts | 10.8 Volts | 11.5 Volts |
| Module Resistance | 3.14 Ohms | 3.27 Ohms | 3.51 Ohms |
| Max Operating Temperature | 80 °C | | |
| Weight | 9.0 gram(s) | | |

Finishing Options

| Suffix | Thickness | Flatness / Parallelism | Hot Face | Cold Face | Lead Length |
|--------|--------------------------------------|--|----------|-----------|---------------------|
| L | 3.581 ± 0.254 mm 0.141 ± 0.010 in | 0.004 mm / 0.004 mm 0.00015 in / 0.00015 in | Lapped | Lapped | 114.3 mm 4.50 in |

Sealing Options

| Suffix | Sealant | Color | Temp Range | Description |
|--------|---------|----------------------|--------------|----------------------------------|
| RT | RTV | Translucent or White | -60 to 204°C | Non-corrosive, silicone adhesive |

Notes

Max operating temperature: 80°C
Do not exceed I_{max} or V_{max} when operating module
Reference assembly guidelines for recommended installation
Solder tinning also available on metallized ceramics

Any information furnished by Tark Thermal Solutions and its agents, whether in specifications, data sheets, product catalogues or otherwise, is believed to be (but is not warranted as being) accurate and reliable, is provided for information only and does not form part of any contract with Tark Thermal Solutions. All specifications are subject to change without notice. Tark Thermal Solutions assumes no responsibility and disclaims all liability for losses or damages resulting from use of or reliance on this information. All Tark products are sold subject to the Tark Thermal Solutions Terms and Conditions of sale (including Tark's limited warranty) in effect from time to time, a copy of which will be furnished upon request.

© Copyright 2025 Tark Thermal Solutions, Inc. All rights reserved.

Revision: 00 Date: 06-01-2022

Print Date: 05-16-2025