

Data sheet

PR015xxVBHC Type 017

Page 1/7


P/N
310171xx

xx=number of poles


2026/03/17

Version: AI


Illustrations



Dimensional drawing as an example



Drill pattern as an example



See enlarged drawings at the end of document

Product specification

- pin header, THR solderable
- centerline 5.00 mm, direction of connection vertical 0°
- fittable without loss of poles
- color black
- Tape & Reel packaging possible



Data sheet

PR015xxVBHC Type 017

Page 2/7

P/N
310171xx

xx=number of poles

2026/03/17

Version: AI

Technical Data

General Data

Solder pin length	3.4 mm		
min. number of poles	2		
max. number of poles	24		
Insulating material class	CTI 400		
clearance/creepage dist.	3.7 mm		
Protection category	IP00		
Rated current	10 A		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250 V	500 V	500 V
Rated test voltage	4 kV	4 kV	4 kV

Approvals

 V / A	300 / 15
approval UL - File No.	E121004
	250 V / 4 kV / 10 A / 1.0 mm

Material

insulating material	PA
flammability class	V0
contact pin material	CuZnPb
contact pin surface	Ni + Ag
Glow-Wire Flammability GWFI	960 °C acc. to IEC 60695-2-12
Glow-Wire Flammability GWIT	775 °C acc. to IEC 60695-2-13

Climatic Data

upper limit temperature	105 °C
lower limit temperature	-40 °C

general

Tolerance	ISO 2768 -mH
Solderability	reflowable

Application note

Data sheet

Page 3/7

PR015xxVBHC Type 017

P/N

310171xx

xx=number of poles

2026/03/17

Version: AI

Technical Data

This product is a standard product of METZ CONNECT. METZ CONNECT is not aware of the specific intended use of the goods by the Customer or any customers of the Customer. The Customer guarantees that it has fully and sufficiently tested the use of the goods and any product modifications, product changes or product enhancements with regard to the specific intended use in accordance with the state of the art or in any other way. At METZ CONNECT's request, the Customer shall submit and make available meaningful evidence (e.g. test and laboratory protocols, certifications, etc.).



Data sheet

PR015xxVBHC Type 017

Page 4/7

P/N

310171xx

xx=number of poles

2026/03/17

Version: AI

Counterpart of

P/N	Designation
310071	RP025xxIBWC Type 007
31007102	RP02502IBWC Typ 007
31007103	RP02503IBWC Typ 007
31007104	RP02504IBWC Typ 007
31007105	RP02505IBWC Typ 007
31007106	RP02506IBWC Typ 007
31007107	RP02507IBWC Typ 007
31007108	RP02508IBWC Typ 007
31007109	RP02509IBWC Typ 007
31007110	RP02510IBWC Typ 007
31007111	RP02511IBWC Typ 007
31007112	RP02512IBWC Typ 007
31007113	RP02513IBWC Typ 007
31007114	RP02514IBWC Typ 007
31007116	RP02516IBWC Typ 007
31007120	RP02520IBWC Typ 007
31007122	RP02522IBWC Typ 007
31007124	RP02524IBWC Typ 007
310261	FT085xxVBFC Type 026
310771	RP025xxIBWU Typ 077
311071	RP025xxHBWC Type 107
31107102	RP02502HBWC Type 107
31107103	RP02503HBWC Type 107
31107104	RP02504HBWC Type 107
31107105	RP02505HBWC Type 107
31107106	RP02506HBWC Type 107
31107107	RP02507HBWC Type 107
31107108	RP02508HBWC Type 107
31107109	RP02509HBWC Type 107
31107110	RP02510HBWC Type 107
31107111	RP02511HBWC Type 107
31107112	RP02512HBWC Type 107
31107114	RP02514HBWC Type 107
31107115	RP02515HBWC Type 107



Data sheet
PR015xxVBHC Type 017

Page 5/7

P/N
310171xx

xx=number of poles

2026/03/17

Version: AI

Counterpart of

31107116	RP02516HBWC Type 107
31107117	RP02517HBWC Type 107
31107118	RP02518HBWC Type 107
ASP025	SP025xxHDNC ASP025
ASP0250204-001	SP02502HDNC ASP0250204-001
ASP0250304-001	SP02503HDNC ASP0250304-001
ASP0250404	SP025xxHDNC ASP025
ASP0250404-004	SP02504HDNC ASP0250404-004
ASP0250504-002	SP02505HDNC ASP0250504-002
ASP0250599-000	SP02505HMNC000 PROFINET
ASP0250804-004	SP02508HDNC ASP0250804-004
ASP145XX22-131	SP145xxHBPC0001
ASP155XX22-131	SP155xxHBPC0001



Data sheet

PR015xxVBHC Type 017

Page 6/7

P/N

310171xx


xx=number of poles

2026/03/17

Version: AI

Illustrations

Dimensional drawing as an example



$L = (\text{pole size} - 1) \times \text{centerline} + 4.8 \text{ mm} [0.189]$

Data sheet
PR015xxVBHC Type 017

Page 7/7

P/N
310171xx
xx=number of poles
2026/03/17
Version: AI

Illustrations

Drill pattern as an example

