

2-Post 12U Heavy-Duty Desktop Server Rack, Small Open Frame 19in Computer Rack, Compact Network Rack for AV / Studio / Data / IT Equipment, TAA Compliant - Free Standing Two-Post Home/Office Rack

Product ID: 2POSTRACK12



This 2-post rack stands on your floor or desktop to provide 12U of storage space for EIA-310-D compliant 19" rack-mount devices, such as telecommunication and A/V equipment. The rack creates a robust storage solution, with support for a total load capacity of 160 kg (350 lb.).

This compact 2-post mounting solution offers a small footprint, and it's engineered to provide exceptional stability, with a total weight capacity of up to 160 kg (350 lb.). The rack fits in virtually any environment, and can be positioned on any surface, such as your floor, desk or table.

The 2-post server rack comes in a flat-packed box to reduce shipping volume, which also significantly reduces your costs in shipping. The rack is packaged efficiently, so you can easily store it for deployment at a later date.

To help make your equipment install easier, this rack includes tool-less clip nuts that seamlessly work with the punched round holes featured on this rack. The tool-less clip nuts provide an easy-to-install nut, unlike square cage nuts which can be a hassle.

The 2POSTRACK12 is backed by a lifetime StarTech.com warranty with free technical support.

Certifications, Reports and Compatibility



Applications

- Use this cabinet to house your A/V equipment in a restaurant or bar, where space may be limited

- Rack-mount the equipment in your repair center or technology shop
- House equipment in audio-video editing rooms, or radio and television broadcast studios

Features

- **2-POST 12U DESKTOP SERVER RACK:** Open frame rack provides a durable, open air housing for 19" rackmount servers/networking/AV/media equipment; Ideal for small home or office spaces without dedicated wiring closets
- **DESIGNED FOR EASY ACCESS:** This free standing desktop network rack is 24.1" (61.3cm) high with a compact profile, and is ideal for environments where frequent front & rear access to equipment like switches and routers is required
- **BUILT TO LAST:** The heavy-duty server rack features heavy gauge mounting rails to ensure a stable installation platform; Supports up to 353.6lb (160kg); Compliant with EIA-RS-310C / EIA/ECA-310-E standards
- **EASY SHIPPING AND ASSEMBLY:** compact flat pack shipping/packaging design to avoid damage and facilitate problem-free installations; Quick and easy setup on a desk, table or floor in your home/office; Ships with cage nuts and screws for mounting equipment
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this TAA compliant Two-Post 12U Computer Open-Frame Rack is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	No
Rack Type	2-Post
Frame Type	Open Frame
U Height	12U
Special Features	Easy Assembly
Mounting Rail Profile	L-Shape
Mounting Hole Types	Circle (For Clip Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity (Stationary)	352.8 lb [160 kg]
------------------------------	-------------------

Physical Characteristics

Color Black

Construction Material Steel

Product Measurements

Product Length 12.0 in [30.5 cm]

Product Width 20.4 in [51.8 cm]

Product Height 24.0 in [61.0 cm]

Weight of Product 15.1 lb [6.9 kg]

Packaging Information

Flat Pack (Assembly Required) Yes

Package Length 28.4 in [72.2 cm]

Package Width 13.9 in [35.2 cm]

Package Height 3.0 in [7.7 cm]

Shipping (Package) Weight 17.5 lb [7.9 kg]

What's in the Box

Included in Package 1 - Right Bracket

1 - Left Bracket

1 - Top Bracket

1 - Bottom Bracket

4 - Rubber Feet

12 - 10-32 Phillips Screws

36 - 10-32 Mounting Screws

36 - Clip Nuts

1 - instruction manual

Warranty Information

Warranty

Lifetime

**Product appearance and specifications are subject to change without notice.*

