

4-Post 15U Mobile Open Frame Server Rack, Four Post 19" Network Rack with Wheels, Rolling Rack with Adjustable Depth for Computer/AV/Data/IT Equipment - Casters, Leveling Feet or Floor Mounting

**Product ID:** 4POSTRACK15U



The 15U open frame rack lets you store your servers, network and telecommunications equipment in a sturdy, adjustable depth open-frame rack.

Designed with ease of use in mind, this 15U 4 post rack offers easy-to-read markings for both rack units (U) and depth, with a wide range of mounting depth adjustments (22 - 40 in.) that make it easy to adapt the adjustable server rack to fit your equipment.

This durable free standing server rack supports a static loading capacity of up to 1200 lb. (544 kg) and portable rolling weight capacity of 660 lb. (300 kg). The rack also features offers compliance with the EIA/ECA-310 standard for a universal design that's compatible with most network equipment rack equipment.

For a complete server storage solution that saves you time and hassle, the mobile server rack includes optional accessories such as casters, leveling feet and cable management hooks. The base is also pre-drilled for securely fastening the rack to the floor if needed, providing you with additional stability while free standing.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## **Certifications, Reports and Compatibility**



## Applications

- Suitable for rack-mount equipment where security at the rack level is not required
- Durable storage for rack-mount servers, KVM switches, and networking equipment
- Rack-mounting A/V equipment in a radio or television studio

## Features

- **ADJUSTABLE DEPTH:** 4-Post 15U 19" open frame server rack with 4 vertical rails and adjustable mounting depth 22" to 40" (56,0cm to 101,7cm); Compatible with various servers / switches / data / AV and other IT equipment; EIA/ECA-310-E Compliant
- **EASY ASSEMBLY:** Mobile network rack with easy-to-follow assembly instructions and online video; Compact flat-pack shipping to avoid damage and facilitate installation; Only 30in (77cm) high, ideal for utility/server closets or narrow home/office spaces
- **COLD ROLLED STEEL:** Durable 4 Post 19" open frame rack designed for ventilation with 15U mounting height and 1200lb (544kg) weight capacity (stationary); 3 install options included: casters, levelling feet, or base-plate to secure rack to the floor
- **HARDWARE INCLUDED:** Rolling computer/data rack includes cage nuts and screws to mount equipment, easy to read Units (U) and depth adjustment markings, cable management hooks for organization, and required assembly tools
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this 15U rack is backed for 2-years, including free lifetime 24/5 multi-lingual technical assistance

---

### Hardware

Warranty	2 Years
Wallmountable	No
Rack Type	4-Post
Frame Type	Open Frame
U Height	15U
Special Features	Adjustable Mounting Rails
	Base Plate with Floor-Anchoring Holes

Built-in Cable Management

Casters (Included)

Grounding Lug(s)

Leveling Feet

Easy Assembly

U-Markings

Mounting Rail Profile      L-Shape

Mounting Hole Types      Square (For Cage Nut)

Industry Standards      EIA/ECA-310-E

---

#### Performance

Weight Capacity (Stationary)      1199.5 lb [544 kg]

---

#### Physical Characteristics

Color      Black

Construction Material      Steel

Product Length      3.7 ft [1.1 m]

Product Width      23.6 in [60.0 cm]

Product Height      30.3 in [77.1 cm]

Weight of Product      60.4 lb [27.4 kg]

Maximum Mounting Depth      40.0 in [101.7 cm]

Minimum Mounting Depth      22.0 in [56 cm]

Product Height with Casters      33.2 in [84.4 cm]

---

#### Packaging Information

Flat Pack (Assembly Required)      Yes

Package Quantity      1

Package Length	11.5 in [29.2 cm]
Package Width	36.7 in [93.3 cm]
Package Height	6.2 in [15.8 cm]
Shipping (Package) Weight	59.0 lb [26.8 kg]

---

#### What's in the Box

Included in Package	4 - Caster
	18 - M6 Flange Nut
	18 - M6 Flat Washer
	18 - M6 Hex Screw
	8 - Cable Management Hook
	8 - Hook Mounting Screw
	2 - Left Vertical Rail
	2 - Right Vertical Rail
	8 - Corner Section
	8 - Center Section
	2 - Top Bracket
	50 - M8 Flat Washer
	50 - M8 Hex Screw
	1 - 10mm Wrench
	1 - 13mm Wrench
	1 - Philips Head Screwdriver
	4 - Philips Head Screw
	4 - Locking Washer
	24 - M6 Screw
	24 - M6 Plastic Washer

24 - M6 Cage Nut

4 - Leveling Feet

4 - Grounding Wire

1 - Manual

---

**Warranty  
Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*