

2ft (60cm) Power Extension Cord, C14 to C13 PDU Power Cord, 10A 250V, 18AWG, Black  
Extension Cable, AC Power Cable for PDU/Power Supply, TAA Compliant, UL Listed

**Product ID:** 8713-8200-POWER-CORD



The IT Pro's Choice

StarTech.com power cables are designed for IT Pro applications and requirements, including standard and heavy-duty power cords, extension cords, medical-grade cords, splitter and passthrough cables. Performance, safety and reliability are ensured by our in-house and third-party testing labs.

StarTech.com offers an extensive range of options in various lengths, connector ends, jacket types and wire gauges.

- Certified for performance and safety: Made from UL listed components to meet UL62 & UL817
- Environmental safety and compliance with REACH and RoHS.
- 100% copper wiring tested for continuity and conductivity ensuring maximum performance and reliability.
- Temperature chamber tested to ensure cable performs to environmental and jacket rating

Backed for life by StarTech.com with 24-hour, five day-a-week support from qualified Technical Advisor and our IT Pro community forums, our brand is trusted throughout the IT ecosystem and used by over 80% of Fortune 500 companies.

## Certifications, Reports and Compatibility



## Applications

- Extend a monitor, scanner, printer, or PC power cord by an additional 2ft
- Extend a power connection from a crowded PDU for more convenient access

## Features

- AC POWER CORD: 2ft (60cm) 18AWG power supply extension cable with IEC 60320 C14 to C13 connectors is suitable for workstations/home office or rack mounted equipment; Extend a C13 power cord to a power supply or PDU; Indoor use; Rated to carry 250V at 10A
- BUILT FOR PERFORMANCE AND SAFETY: UL Listed; VW-1 Fired Rated cable with fully molded strain reliefs for durability; 3-conductor power cable made with 100% copper wire
- SPECS: 2ft (60cm); TAA Compliant; IEC 60320 C14 to IEC 60320 C13; 18AWG; 250V 10A (Max); Jacket Rating: SJT; Color: Black; Temperature Range: -4F to 221F (-20 to 105); Cable O.D.: 0.3in (7.8mm)
- COMPATIBILITY: PC Power Cord IEC 60320 C14 works with North American PDUs and cables; IEC C13 connector works with most desktop computers, servers, PDUs, UPS, printers, and more; Replacement PC power supply cable/cord
- THE IT PRO'S CHOICE: Designed and built for IT Professionals, this computer power cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance; This C14 to C13 power cord is available in other lengths

---

### Hardware

Warranty	Lifetime
Number of Conductors	3
Connector Plating	Nickel
Cable Jacket Material	PVC
Fire Rating	VW-1 Rated
Cable Type	SJT

---

### Performance

Maximum Cable Length	2.0 ft [0.6 m]
----------------------	----------------

---

### Connector(s)

Connector A	1 - IEC 60320 C14 Power
Connector B	1 - IEC 60320 C13 Power

---

### Power

Input Voltage	250 AC
---------------	--------

---

Input Current	10A
---------------	-----

---

#### **Environmental**

Operating Temperature	-20 to 105C (-4 to 221F)
Storage Temperature	-20 to 105C (-4 to 221F)
Humidity	0% to 65% RH

---

#### **Physical Characteristics**

Color	Black
Wire Gauge	18 AWG
Cable Length	2.0 ft [0.6 m]
Cable OD	0.3 in [7.8 mm]
Product Length	24.0 in [61.0 cm]
Product Width	1.1 in [2.9 cm]
Product Height	0.8 in [2.1 cm]
Weight of Product	3.2 oz [92.0 g]

---

#### **Packaging Information**

Package Length	8.2 in [20.8 cm]
Package Width	3.3 in [8.4 cm]
Package Height	1.4 in [3.6 cm]
Shipping (Package) Weight	3.5 oz [98.0 g]

---

#### **What's in the Box**

Included in Package	1 - 2ft C14 to C13 Power Extension Cord
---------------------	---

---

#### **Warranty Information**

Warranty	Lifetime
----------	----------

---

*\*Product appearance and specifications are subject to change without notice.*