

1000 Mbps Gigabit Single Mode Fiber Media Converter LC 40 km - TAA

Product ID: ET1000S40LC2



The ET1000S40LC2 1000 Mbps Gigabit Single-Mode Fiber Media Converter (LC, 40 km) enables you to extend a Gigabit Ethernet network over single-mode fiber, at distances up to 40km (25 miles).

A cost-effective solution for connecting a Gigabit Ethernet (1000Base-T) network to remote network segments over a (1000Base-LX/SX) fiber backbone, the GbE to SM fiber converter supports full Gigabit speeds for ideal network performance and scalability. Designed to offer a durable and convenient Ethernet to fiber solution, the Ethernet to LC Fiber converter features an all-steel chassis, and a simple plug-and-play installation with minimal configuration required.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Provides connectivity to a user or network segment that is in an isolated area of a large complex or in another building altogether
- Perfect for secure connections required by government agencies where EMI is not acceptable
- Connect traffic control/monitoring systems at extreme distances to the main office
- Extend network connectivity to remote areas of stadiums, auditoriums or other venues

- Converts 1000Base-LX fiber optic signals to 1000Base-T Ethernet over single mode fiber cable

Features

- Advanced features include Link-loss forwarding, remote monitor status, two frame lengths
- Maximum Fiber Cable length of 40 Km
- Supports full or half-duplex operation
- Easy installation

Hardware

| | |
|--------------------|---|
| Warranty | 2 Years |
| PoE | No |
| WDM | No |
| Industry Standards | IEEE802.3ab (1000BASE-T) IEEE802.3z (1000BASE-SX/LX) |

Performance

| | |
|----------------------------|------------------------------|
| Maximum Data Transfer Rate | 2000 Mbps (full duplex mode) |
| Max Transfer Distance | 40 km (24.8 mi) |
| Type | Single Mode |
| Wavelength | 1310nm |
| Fiber Operating Mode | Half/Full-Duplex |
| Auto MDIX | Yes |
| Jumbo Frame Support | 9K max. |
| MTBF | 65,000 Hours |

Connector(s)

| | |
|-----------------------|--|
| Local Unit Connectors | 1 - Fiber Optic LC Duplex 1 - RJ-45 |
|-----------------------|--|

Power

| | |
|------------------------------|---------------------|
| Power Source | AC Adapter Included |
| Input Voltage | 100 - 240 AC |
| Input Current | 0.36A |
| Output Voltage | 12V DC |
| Output Current | 1.6 A |
| Center Tip Polarity | Positive |
| Plug Type | M |
| Power Consumption (In Watts) | 4 |

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 60C (32F to 140F) |
| Storage Temperature | -10C to 70C (14F to 158F) |
| Humidity | 10~90% RH |

Physical Characteristics

| | |
|-------------------|------------------|
| Color | Black |
| Material | Steel |
| Product Length | 6.1 in [15.5 cm] |
| Product Width | 3.4 in [8.7 cm] |
| Product Height | 0.9 in [2.4 cm] |
| Weight of Product | 14.4 oz [407 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 5.4 in [13.7 cm] |
| Package Width | 8.1 in [20.6 cm] |
| Package Height | 3.6 in [9.1 cm] |
| Shipping (Package) Weight | 1.7 lb [0.8 kg] |

What's in the Box

| | |
|---------------------|---|
| Included in Package | 1 - Fiber Media Converter |
| | 1 - Universal power adapter: comes ready for NA/EU/UK only when you buy in NA/EU/UK; comes ready for Australia and New Zealand only when you buy in Australia and New Zealand |
| | 1 - Grounding Screw |
| | 1 - Instruction Manual |

**Warranty
Information**

| | |
|----------|---------|
| Warranty | 2 Years |
|----------|---------|

****Product appearance and specifications are subject to change without notice.***

