

Industrial RS232 to RS422/485 Serial Port Converter with 15KV ESD Protection

Product ID: IC232485S



The IC232485S Industrial RS232 to RS-422/485 Serial Converter is a bi-directional adapter that lets you adapt an RS232 data signal to either RS485 (2 or 4-wire) or RS422 and vice-versa, with support for baud rates up to 921.6 Kbps.

Ideal for industrial environments, the serial port converter provides 15KV ESD protection on all signal pins to protect costly and often sensitive control equipment against electrical damage. The serial converter also features a sturdy wall-mountable metal housing with Power, Tx and Rx LED indicators for simple status monitoring.

The adapter supports auto baud rate detection as well as RS-422 and RS485 mode detection, with an integrated dip switch for manual mode selection if needed, and supports connection distances of up to 4000ft (1200m).

Backed by a 2-year StarTech.com warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Monitor or control RS-422/485 serial devices like PLCs and other industrial equipment
- Adapt and connect a scale, meter, scanner or one of several other control peripherals to a computer system with only RS232

## Features

- RS232 to 2/4-wire RS485 or RS422 conversion
- Supports RS422 and RS485 auto detect and manual switching
- 15KV ESD protection on all signal pins
- Supports baud rates up to 921.6 Kbps
- Wall-mountable
- Supports a maximum connection distance of 4000ft (1200m)

**Hardware**

Warranty	2 Years
Ports	1
Interface	Serial
Port Style	External Hub

**Performance**

Maximum Cable Length	3936.0 ft [1200 m]
Serial Protocol	RS-232/422/485
Max Baud Rate	921.6 Kbps

**Connector(s)**

Connector Type(s)	1 - DB-9 (9 pin, D-Sub)
	1 - DB-9 (9 pin, D-Sub)

**Indicators**

LED Indicators	1 - Power (Green)
	1 - Rx (Yellow)
	1 - Tx (Yellow)

**Power**

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	0.5 A

Output Voltage	5 DC
Output Current	1 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	5

---

**Environmental**

Operating Temperature	0C to 50C (32F to 122F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	5~85% RH

---

**Physical Characteristics**

Color	Black
Material	Steel
Product Length	3.3 in [8.4 cm]
Product Width	2.9 in [7.3 cm]
Product Height	0.9 in [2.2 cm]
Weight of Product	5.0 oz [143 g]

---

**Packaging Information**

Package Quantity	1
Package Length	4.7 in [11.9 cm]
Package Width	7.4 in [18.9 cm]
Package Height	2.8 in [7.1 cm]
Shipping (Package) Weight	12.2 oz [346.0 g]

---

**What's in the Box**

Included in Package	1 - RS-232 to RS-422/485 Converter
	1 - Universal Power Adapter (NA/EU/UK)

1 - Instruction Manual

---

**Warranty  
Information**

Warranty	2 Years
----------	---------

---

*\*Product appearance and specifications are subject to change without notice.*

