


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

8 7 6 5 4 3 2 1

| REVISIONS | | | |
|-----------|-----------------|-----------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 1/25/2022 | JJOHNSTON |
| | | | |
| | | | |
| | | | |



| PART NUMBER | LENGTH METER [FEET] |
|----------------|---------------------|
| FCA-SSCASTAD2 | 2.0 [6.56] |
| FCA-SSCASTAD5 | 5.0 [16.40] |
| FCA-SSCASTAD10 | 10.0 [32.81] |
| FCA-SSCASTAD15 | 15.0 [49.21] |

NOTES:

1. SC CONNECTOR 2 ASSEMBLY POLISH TYPE: APC.
2. ST CONNECTOR 2 ASSEMBLY POLISH TYPE: APC.
3. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.


REGULATORY COMPLIANCE:

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES [mm]

OVERALL CABLE LENGTH TOLERANCE:
 ≤ 12 [305] = $+1$ [25] / -0
 > 12 [305] ≤ 60 [1524] = $+2$ [51] / -0
 > 60 [1524] ≤ 120 [3048] = $+4$ [102] / -0
 > 120 [3048] ≤ 300 [7620] = $+6$ [152] / -0
 > 300 [7620] = $+5\%$ / -0

ALL OTHER DIMENSIONAL TOLERANCES:
 $.X = \pm .2$ [5] FRACTIONS
 $.XX = \pm .02$ [5] $\pm 1/32$
 $.XXX = \pm .005$ [1.3] ANGLES $\pm 1^\circ$



APPROVALS
DRAWN BY
DMAY
CHECKED BY
JJOHNSTON
APPROVED BY
JJOHNSTON

DATE
1/18/22
1/25/22
1/25/22

CATEGORY

L-com
an INFINITe brand

50 High Street, West Mill,
North Andover, MA 01845 USA.
Phone: 1.800.341.5266
1.978.682.6936

FIBER OPTICS

PRODUCT DESCRIPTION
FIBER OPTIC PATCH CORD SM G652D DUPLEX
SC/APC-ST/APC ARMORED 4.8mm LSZH BLACK

| | | | |
|------------------|-------------------------------|--------------------------|------------------|
| SIZE A | CAGE CODE 43321 | ITEM NO. FCA-SSCASTAD | REV. A |
| SCALE: NONE | CAD FILE: FCA-SSCASTAD.SLDDRW | SHEET 1 OF 1 | |