

25 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

**Product ID:** MXT101HQ\_25



This 25ft High Resolution VGA Extension Cable is designed to provide the highest video quality possible through VGA.

Ideally suited for high resolution VGA applications, this high quality male to female coaxial VGA extension cable helps to eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables, and provides superior EMI interference protection by using ferrite cores near the connector ends.

## Certifications, Reports and Compatibility



## Applications

- Extends your VGA monitor cable

## Features

- Ideal for high resolution monitors (1920x1200 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Triple-coaxial + twisted-pair wire for crystal clear display

- Ferrite core eliminates EMI interference

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel

---

**Connector(s)**

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - VGA (15 pin, High Density D-Sub)

---

**Special Notes / Requirements**

Note	Pin number 9 is not populated on these connectors
------	---

---

**Physical Characteristics**

Color	Black
Wire Gauge	28 AWG
Cable Length	25.0 ft [7.6 m]
Product Length	25.0 ft [7.6 m]
Weight of Product	27.6 oz [782 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.6 in [21.9 cm]
Package Width	9.9 in [25.2 cm]
Package Height	2.5 in [64 mm]
Shipping (Package) Weight	1.8 lb [0.8 kg]

---

**What's in the Box**

Included in Package	1 - 25 FOOT COAXIAL CABLE
	2 - Nuts

---

**Warranty**

**Information**

Warranty      Lifetime

---

***\*Product appearance and specifications are subject to change without notice.***

