

10 M Outdoor Rated Type N to 7/16 DIN M/M  
Right Angle SPO-250 Low PIM Cable Jumper

**CASPO250012-10M**




**Configuration**

- Connector 1: 7/16 DIN Male Right Angle
- Connector 2: N Male
- Cable Type: SPO-250

**Features**

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- PE Jacket
- Shielding Effectivity > 100 dB
- 100% Tested with PIM Test Results Marked on Cable
- 1.25 Inch Minimum Bend Radius
- Low Loss with Excellent VSWR



**Applications**

- Distributed Antennas Systems (DAS)
- Outdoor Installations
- Low PIM Applications
- Multi-Carrier Communication Systems

**Description**

PolyPhaser CASPO250012-10M is a 10 M Outdoor Rated Type N to 7/16 DIN M/M Right Angle SPO-250 Low PIM Cable Jumper built using high quality components by skilled technicians to ensure a reliable product. The Type N Male to 7/16 DIN Male Right Angle jumper connections are designed to industry standard interface dimensions to ensure superior performance. These low PIM corrugated cable assemblies are durable and outdoor rated for applications that require these parameters. All PolyPhaser cable assemblies are available for same day shipment to fulfill your urgent needs. This high-quality RF coaxial assembly is perfect in many RF Interconnect applications such as distributed antenna systems (DAS), outdoor installations, low PIM applications, and many other RF systems. The CASPO250012-10M Type N to 7/16 DIN low PIM cable assembly is the perfect companion to PolyPhaser line of products, particularly when used as an antenna jumper.

The quarter inch low PIM outdoor rated coax used in these Type N to 7/16 DIN assemblies is a .250 inch diameter copper corrugated coax with a black PE jacket. This cable's foam PE dielectric is low loss material with a phase velocity of 83% and offers excellent passive intermodulation (PIM) performance better than -160 dBc. The construction of the quarter inch copper corrugated jumper results in a minimum bend radius of 1.25 inches. The cable assembly's combination of Type N to 7/16 DIN M/M Right Angle and Times Microwave's SPO-258 low PIM plenum rated cable supports a maximum operation frequency of 5.8 GHz. Each cable assembly is installed with heat shrink booting on each end and a PIM label with the measured PIM level. You can find detailed performance specifications in the product datasheet. All PolyPhaser assemblies are tested and inspected prior to shipping.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
[10 M Outdoor Rated Type N to 7/16 DIN M/M Right Angle SPO-250 Low PIM Cable Jumper CASPO250012-10M](#)

10 M Outdoor Rated Type N to 7/16 DIN M/M  
Right Angle SPO-250 Low PIM Cable Jumper



## CASPO250012-10M

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		83		%
Passive Intermodulation			-160	dBc
Capacitance		24 [78.74]		pF/ft [pF/m]
Inductance		0.054 [0.18]		uH/ft [uH/m]

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.45	0.7	1	2.5	5.8	GHz
Insertion Loss (Max.)	16.31	19.79	25.68	40.93	65.9	dB

**Electrical Specification Notes:**

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly. Insertion Loss is estimated as 0.1 dB for the right angle connector and  $0.1 \cdot \sqrt{FGHz}$  dB for the straight connector.

### Mechanical Specifications

**Size**

Length	393.7 in [10 m]
Diameter	1.14 in [28.96 mm]
Weight	2.006 lbs [909.91 g]

**Cable**

Cable Type	SPO-250
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	Foam PE
Number of Shields	1
Shield Layer 1	Helically Corrugated Copper Tube
Outer Conductor Material and Plating	Copper
Outer Conductor Diameter	0.252 in [6.4 mm]
Jacket Material	PE, Black
Jacket Diameter	0.303 in [7.7 mm]
One Time Minimum Bend Radius	1.25 in [31.75 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:  
[10 M Outdoor Rated Type N to 7/16 DIN M/M Right Angle SPO-250 Low PIM Cable Jumper CASPO250012-10M](#)

10 M Outdoor Rated Type N to 7/16 DIN M/M  
Right Angle SPO-250 Low PIM Cable Jumper



## CASPO250012-10M

Bending Moment 0.5 lbs-ft [0.68 N-m]

### Connectors

Description	Connector 1	Connector 2
Type	7/16 DIN Male Right Angle	N Male
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Silver	Phosphor Bronze, Silver
Contact Plating Specification	196 µin	196 µin
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Tri-Metal
Body Plating Specification	118 µin	118 µin
Coupling Nut Material and Plating	Brass, Nickel	Brass, Tri-Metal
Coupling Nut Plating Specification	118 µin	118 µin
Torque	22.127 ft-lbs [30 Nm]	9.74 in-lbs [1.1 Nm]

### Environmental Specifications

#### Temperature

Operating Range -40 to +85 deg C  
Storage Range -40 to +85 deg C

### Compliance Certifications

#### Plotted and Other Data

Notes:

- Values at 25°C, sea level.

PolyPhaser protects and increases the reliability of global RF communications networks, including transportation, telecommunications, defense, security and industrial applications, with superior RF surge protection technologies including DC Block, DC Pass and Ultra Low PIM. Backed by responsive service and expert technical support PolyPhaser continually expands its product offering and services to serve engineers' urgent needs for RF components in mission critical communication networks.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10 M Outdoor Rated Type N to 7/16 DIN M/M Right Angle SPO-250 Low PIM Cable Jumper CASPO250012-10M](https://www.polyphaser.com/10-m-outdoor-rated-type-n-to-7-16-din-m-m-right-angle-spo-250-low-pim-cable-jumper-p.aspx)

URL: <https://www.polyphaser.com/10-m-outdoor-rated-type-n-to-7-16-din-m-m-right-angle-spo-250-low-pim-cable-jumper-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [10 M Outdoor Rated Type N to 7/16 DIN M/M Right Angle SPO-250 Low PIM Cable Jumper CASPO250012-10M](https://www.polyphaser.com/10-m-outdoor-rated-type-n-to-7-16-din-m-m-right-angle-spo-250-low-pim-cable-jumper-p.aspx)



10 M Outdoor Rated Type N to 7/16 DIN M/M  
Right Angle SPO-250 Low PIM Cable Jumper

## CASPO250012-10M



make modifications to the part and/or the documentation of the part, in order to implement improvements. PolyPhaser reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. PolyPhaser does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and PolyPhaser does not assume any liability arising out of the use of any part or documentation.

