


2-Port 2.5Gbps NBASE-T PoE Network Card, Dual Intel I225-V, 802.3af/at PoE+ Multi-Gigabit NIC, PCI Express Server LAN Card, LP4/8-Pin PCIe-Powered

Product ID: PR22GIP-NETWORK-CARD



This 2.5 GbE network interface card (NIC) features dual Intel I225-V chipsets with Intel vPro technology to enhance performance and data integrity. The variable multispeed options (2.5/1Gbps and 100/10Mbps) enable support for both new and legacy network hardware. Utilize existing CAT5e or CAT6 cabling infrastructure while adding NBASE-T (802.3bz) compatibility for seamless integration.

The PCIe Ethernet card supports the IEEE 802.3af and IEEE 802.3at (Type 1 and Type 2) standards for Power Sourcing Equipment (PSE) and can deliver up to 48V DC and 25.5W of power per port to compliant Powered Devices (PD). This flexibility eliminates the need for a separate power supplies or PoE injectors for remote networked devices such as IP cameras, access control devices, remote kiosks, and wireless access points.

The PCIe network card leverages Intel vPro technology for remote management and troubleshooting capabilities. Improve bandwidth for data-intensive applications, network sharing, FTPs, online or local storage/backup, and the streaming of online content - while reducing network slowdowns. Access up to 2.5GBASE-T speeds using Cat5e (or better) cabling, to maximize existing networks and equipment.

The network interface card connects through an available PCI Express x2 2.0 (or higher) expansion slot. The card ships with a standard-profile bracket pre-installed and includes a low-profile bracket for installation into small form factor systems and servers. This ethernet NIC card is compatible with Windows, Windows Server, VMware, and Linux.

This card supports the following advanced features: PXE Boot, WoL, VLAN tagging, 9K jumbo frame, full-duplex, and Intel vPro technology.

Certifications, Reports and Compatibility



Applications

- Connect Power over Ethernet enabled IP cameras, phones, or Wireless Access Points
- Provide power to remote powered devices that require a PoE power source
- Add multi-gigabit connectivity to a desktop or server

Features

- **2-PORT 2.5G POE ETHERNET CARD:** High-performance PCIe 2.5Gbps network card with dual Intel I225-V chips; Leverage existing Cat5e/Cat6 cabling (or better) without the use of a Power over Ethernet injector; NBASE-T compatible (802.3bz); PCI Express 2.0 x2
- **POE+ COMPLIANT:** Ethernet NIC provides up to 30W PSE and 25.5W PD per port at 48V DC to connected devices; Supports IEEE 802.3af (PoE) and 802.3at (PoE+) to power remote devices such as access points, RFID readers, and IP cameras
- **IT MANAGEMENT:** Intel vPro for remote management and troubleshooting; PXE boot enabled for centralized OS deployment and updates; 9K jumbo frame for reduced packet overhead; Remote system boot via WoL; VLAN support for efficient network management
- **BUILD QUALITY:** LAN card features built-in heatsink to keep controller chips running cool and for optimal performance, LED indicators for link status/speed, and LAN transformers maintain signal quality and reduced EMI for reliable communication
- **COMPATIBILITY:** 2.5GBASE-T variable speed options (2.5G/1G/100M/10M) with auto-negotiation; Multi-gigabit network interface card for PC is compatible with Windows, Windows Server, VMware, and Linux; Low profile bracket included for hardware compatibility

Hardware

Warranty	2 Years
Ports	2
Interface	RJ45 (2.5G Ethernet)
Bus Type	PCI Express
Card Type	Standard Profile (LP bracket incl.)

Industry Standards	IEEE 802.3at Power over Ethernet IEEE 802.3af Power over Ethernet IEEE 802.3bz (2.5GBASE-T) IEEE 802.3ab (1000BASE-T) IEEE 802.3u (100BASE-TX) IEEE 802.3i (10BASE-TX) IEEE 802.1Q (VLAN) IEEE 802.1p (QoS) IEEE 802.1AS (AVB) IEEE 802.1X (WoL) IEEE P802.3az (EEE) IEEE 1588 (PTP) PCI Express Version 2.0
Chipset ID	Intel - I225-V

Performance

Wake On Lan	Yes
Maximum Data Transfer Rate	2.5Gbps
Compatible Networks	2.5G/1G/100Mbps/10Mbps
Auto MDIX	Yes
PXE	Yes
Full Duplex Support	Yes
Jumbo Frame Support	9K max.
Promiscuous Mode	Yes

Connector(s)

Connector Type(s)	1 - PCI Express x2
Internal Ports	1 - 4 pin Power (LP4) Female 1 - 8 pin (6+2) PCIe Power Female
External Ports	2 - RJ-45 (PoE+)

Software

OS Compatibility	Windows 10, 11 Windows Server 2019, 2022 Linux 5.8.x and up - LTS Versions only VMware ESXi 7.0
------------------	---

Special Notes / Requirements

Note	- Intel NIC Teaming is supported only on Windows Server OS (e.g., Server 2012, 2016) and not on desktop versions like Windows 10 or 11.
------	---

Indicators

LED Indicators	2 - Left LED Indicator is Link Status Solid Green: Active Link Flashing Green: Activity
	2 - Right LED Indicator is Link Speed Solid Green: 2.5 Gbps Solid Amber: 1.0 Gbps Off: 100 or 10 Mbps

Power

Power Source	Bus Powered
Output Voltage	48 DC

Environmental

Operating Temperature	0C to 55C (32F to 131F)
Storage Temperature	10C - 70C (14F - 158F)
Humidity	5% - 90% RH

Physical Characteristics

Color	Black
Product Length	7.1 in [18.0 cm]
Product Width	4.8 in [12.1 cm]
Product Height	0.8 in [2.2 cm]
Weight of Product	3.9 oz [111 g]

Packaging Information

Package Length	5.7 in [14.4 cm]
Package Width	8.1 in [20.7 cm]
Package Height	1.5 in [3.8 cm]
Shipping (Package) Weight	3.7 oz [106.0 g]

What's in the Box

Included in Package	1 - Network Card
	1 - Low Profile Bracket
	1 - Quick-Start Guide

**Warranty
Information**

Warranty

2 Years

****Product appearance and specifications are subject to change without notice.***