

Data Surge Protector SPD CPX Indoor 8 Port 10/100 Base-T Ethernet RJ45 GDT, TBU, UL 497A



1101-987

Features

- UL 497B
- Configurable Mixed Signal Protection
- RJ-45 Connectivity
- Loaded with 8 Fused 109/100BT Protection Modules
- Fused and Non-Fused Options
- Rack Mount

Applications

- 10/100 Base-T Ethernet Networks
- Telecommunications Base Stations
- WISP/ISP
- IT & Data Centers
- Point-to-Point Links
- Control Lines and Sense Loops
- Oil & Gas

Description

Data surge protector (also known as SPD or lightning protector) 1101-987 from Transtector is an indoor style SPD that utilizes state of the art TBU/GDT technology to protect critical equipment in 10/100 Base-T Ethernet protocol data networks while remaining transparent to data throughput. This surge protector provides effective protection against electrical transient surges that are generated both by external lightning events and by internal switching events and supports long-term system reliability by absorbing high amounts of transient energy while maintaining a very low clamping voltage. Transtector Data Signal surge protectors are available in stock with same day shipping.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Connectors		RJ45		
Compatible Cables		Cat5/5e UTP		
Data Protocols		10/100 Base-T Ethernet		
Data Rate			100	Mb/s
Series Impedance (Data) 1			9	Ohms
Capacitance (Common)			3	pF
Vdc Rating (Data)		5	11	Vdc

Surge Protection Specification

Description	Minimum	Typical	Maximum	Units
Surge Protection Technology		GDT, TBU		
Protected Pins		[1,2], [3,6]		
Protection Modes		L-G, L-L		
10/1000µs Surge Current				
L-G			100	A
8/20µs Surge Current				
L-G			20	kA

Data Surge Protector SPD CPX Indoor 8 Port 10/100 Base-T Ethernet RJ45 GDT, TBU, UL 497A



1101-987

Surge Protection Specification

Description	Minimum	Typical	Maximum	Units
Response Time			75	ns

Mechanical Specifications

Size

Length	1.75 in	[44.45 mm]
Width/Diameter	19 in	[482.6 mm]
Height	3.3 in	[83.82 mm]
Weight	3 lbs	[1.36 kg]

Environmental Specifications

Temperature

Operating Temperature	-40 to +75 deg C
Storage Temperature	-40 to +75 deg C

Installation

Mount Type	19" Rack
Installation Hardware	12-24 X 3/4" PH Phillips
Grounding	Dual 1/4" x 20 Studs

Compliance Certifications

UL Compliant	Yes
Certifications	UL 497A

Transtector Systems specializes in protection of highly sensitive, low voltage equipment through its patented, non-degrading silicon diode technology and custom filters. Our power quality expertise translates into a diverse product offering including AC, DC, and signal applications as well as integrated cabinets, power distribution panels and EMP hardened devices.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Data Surge Protector SPD CPX Indoor 8 Port 10/100 Base-T Ethernet RJ45 GDT, TBU, UL 497A 1101-987](https://www.transtector.com/data-surge-protector-spd-cpx-indoor-8-1101-987)

URL: <https://www.transtector.com/data-surge-protector-spd-cpx-indoor-8-1101-987>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Transtector reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Transtector does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Transtector does not assume liability arising out of the use of any part or document.

1101-987 CAD Drawing

Data Surge Protector SPD CPX Indoor 8 Port 10/100 Base-T Ethernet RJ45 GDT, TBU, UL 497A

