

2U Vertical Wall Mount Patch Panel Bracket - Steel Rack Mount Bracket w/Hardware for 19" Network, Server and Data Equipment - TAA

Product ID: RK219WALLV



The RK219WALLV 2U 19in Steel Vertical Wall Mount Equipment Rack Bracket offers a versatile storage solution allowing rackmount equipment (Network devices, power strips, patch panels) to be mounted vertically (flush with wall) to save space. Alternatively, the 2U bracket can be installed horizontally under a desk, making it easy to access installed equipment directly from your workspace. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

Perfect for SoHo (small office, home office) environments, the wallmount bracket features a sturdy steel design constructed to EIA-310 19in rack standards, and offers space-savings for environments lacking the footprint space for a full size server equipment rack. Suitable for mounting on virtually any wall/ceiling surface (e.g. drywall), the bracket mounting holes are positioned at exactly 16in apart, matching standard construction framework.

Need more storage space? StarTech.com also offers a 3U 19in Wallmount Bracket and a 4U 19in Wallmount Bracket.

Certifications, Reports and Compatibility



Applications

- Mount networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Ideal for small and medium businesses needing rack solutions

Features

- **VERSATILE FUNCTIONALITY:** This multi-use 2U vertical patch panel bracket enables you to mount your server, data, networking or AV equipment vertically on a wall or horizontally under a desk for added versatility
- **STURDY DESIGN:** Constructed to EIA-310 19in rack standards, the black wall mount patch panel bracket features a solid steel design for ultimate durability; the rack can hold up to 125.3lb (56.7kg) to ensure your equipment is secure
- **NO ASSEMBLY REQUIRED:** The open frame, L-shaped rack arrives fully assembled with cage screws for mounting equipment and 1 " screws for mounting the rack to wood surfaces; it's a convenient solution for all your SoHo (small office/home office) rack needs
- **STANDARDIZED HOLE SIZING:** The wall mounting holes on the 2U vertical mountable rack bracket are 16" center to center to provide greater stability and match standard wall studs; it works with most 19" rack mountable equipment for ultimate compatibility
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this patch panel bracket is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	2U
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	125.0 lb [56.7 kg]
-----------------	--------------------

Special Notes / Requirements

Note	Package includes 1 " screws for mounting to wood surfaces, additional hardware will be required for other materials
------	---

Physical Characteristics

Color Black

Construction Material Steel

Product Measurements

Product Length 5.9 in [15.1 cm]

Product Width 19.8 in [50.4 cm]

Product Height 4.1 in [10.5 cm]

Weight of Product 1.7 lb [0.7 kg]

Packaging Information

Flat Pack (Assembly Required) No

Package Length 6.7 in [16.9 cm]

Package Width 21.3 in [54.0 cm]

Package Height 4.7 in [12.0 cm]

Shipping (Package) Weight 2.7 lb [1.2 kg]

What's in the Box

Included in Package 1 - Vertical Wall Mount Bracket

8 - M5 Cage Nuts

8 - M5 Screws

6 - Wood Screws

1 - Instruction Manual

Warranty Information

Warranty Lifetime

**Product appearance and specifications are subject to change without notice.*