

6U Wall Mount Patch Panel Bracket – 19 in – Steel - Vertical Mounting Bracket for Networking and Data Equipment - TAA

Product ID: RK619WALLV



This wall-mount bracket provides 6U of storage space to vertically mount your equipment on the wall. The 6U wall-mount rack is EIA-310-D compliant to ensure compatibility with any 19" rack-mount equipment, such as your power strips, telecommunication, network and A/V devices.

The 6U rack optimizes your working space by mounting equipment to your wall instead of taking up desk space or other surface area. It's perfect for your SoHo (small office, home office) environment, server room or any other location where available space is limited.

The wall rack is constructed of solid steel to ensure a sturdy and safe mounting solution for your expensive, mission-critical equipment. Also, because the wall mounting holes are positioned 16" apart, it exactly matches standard drywall construction framework to ensure simple and secure wall-stud anchoring. Cage nuts and screws are also included with the wall-mount bracket, to save you the hassle of sourcing separate mounting hardware.

To provide a suitable mounting solution for virtually any surface such as your wall, ceiling or desk, the 6U bracket features separate mounting patterns for both ceilings and walls. This means that you can mount the bracket vertically to your wall or horizontally to your ceiling or under your desk.

If you're looking for a mountable storage solution with fewer rack units, StarTech.com also offers a 1U wall-mount bracket, a 2U wall-mount bracket, a 3U wall-mount bracket and a 4U wall-mount bracket.

The RK619WALLV is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Install networking and telecommunication equipment flush against the wall
- Mount KVM switches or workstations under a desk or work bench to free up work space
- Use in your small office environment where you can't comfortably fit a full-sized rack

Features

- **NO ASSEMBLY REQUIRED:** For added convenience, this 6U wall mount patch panel bracket arrives fully assembled with cage screws and nuts for mounting equipment
- **BUILT TO LAST:** Constructed to EIA-310 19in rack standards, the wall mount bracket features a solid steel design for ultimate durability
- **VERSATILE FUNCTIONALITY:** This multi-use patch panel bracket enables you to mount your server or networking equipment vertically on a wall or horizontally under a desk for added versatility
- **STANDARDIZED HOLE SIZING:** Wall mounting holes are 16 inches center to center for greater stability, and mounting to standard wall studs
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this wall mount patch panel bracket is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Wallmountable	Yes
Rack Type	2-Post
Frame Type	Open Frame
U Height	6U
Mounting Rail Profile	L-Shape
Mounting Hole Types	Square (For Cage Nut)
Industry Standards	EIA/ECA-310-E

Performance

Weight Capacity	200.0 lb [90.7 kg]
-----------------	--------------------

Special Notes / Requirements

Note	Package includes 1" screws for mounting to wood surfaces, additional hardware will be required for other materials
------	--

Physical Characteristics

Color	Black
Construction Material	Steel

Product Measurements

Product Length	6.0 in [15.2 cm]
Product Width	19.9 in [50.5 cm]
Product Height	11.1 in [28.2 cm]
Weight of Product	2.9 lb [1.3 kg]

Packaging Information

Flat Pack (Assembly Required)	No
Package Length	12.0 in [30.6 cm]
Package Width	21.5 in [54.7 cm]
Package Height	6.7 in [17.1 cm]
Shipping (Package) Weight	4.9 lb [2.2 kg]

What's in the Box

Included in Package	1 - Vertical Wallmount Bracket
	16 - M5 Cage Nuts
	16 - M5 Screws
	6 - Wood Screws
	1 - Instruction Manual

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

