

Thunderbolt 3 Dock, Dual Monitor 4K 60Hz TB3 Laptop Docking Station, DisplayPort, 85W PD, 3x USB, GbE

**Product ID:** TB3DK2DPPD



Easily transform your Thunderbolt 3 equipped MacBook Pro or Windows laptop into a dual-4K workstation with up to 40Gbps of throughput. The high-quality TB3 dock features three USB 3.0 ports, 85W Power Delivery to charge your laptop.

Great for video editing and other Ultra HD tasks, this dual-4K monitor docking station supports 40Gbps speeds and 4K resolution on two monitors. Run resource-demanding applications on two independent displays, without draining system resources.

Connect your laptop to:

- 1 x 4K monitor via the DP Port
- 1 x 4K monitor via the TB3 USB-C Port (1.8 m cable included)

OR

- 1 x 5K monitor via the DP & TB3 USB-C port

Simply connect the TB3 dock to your laptop with included TB3 cable and start working immediately. No time-consuming driver installations are required.

With three USB 3.0 ports, the Thunderbolt 3 docking station gives you plenty of ports for the latest and legacy devices. Connect USB devices like flash drives using the two Type-A ports. Keep your mobile device charged with the dock's Fast-Charge and sync port. Connect a USB-C device with the USB-C port (5Gbps - data only).

The Thunderbolt 3 docking station features a 170W power adapter supporting Power Delivery to power and charge (up to 85W) your laptop, while powering all your devices connected to the dock. This eliminates the need to use two separate power adapters for your laptop and dock.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the

market that works with a wide range of IT connectivity accessories. The software suite includes:

Advanced Windows Layout Utility: To setup and save custom windows layouts.

Mac Address Pass-Through Utility: To improve network security.

USB Event Monitoring Utility: To track and log connected USB devices

Wi-Fi Auto Switch Utility: Enabling users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit:  
[www.StarTech.com/Connectivity-Tools](http://www.StarTech.com/Connectivity-Tools)

TB3DK2DPPD features a rugged aluminum casing and is backed by a StarTech.com 3-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Review/edit images or media files on two 4K displays
- Transfer a 4K movie in under 30 seconds
- Transfer 3 hours of 4K GoPro video in less than a minute
- Dock and undock quickly, with a single cable for data, power, and external displays

## Features

- NEW VERSION AVAILABLE: Replaced by TB3CDK2DH; Driverless setup for plug-and-play installation; 40Gbps video/data bandwidth; Dual monitor 4K 60Hz; USB Power Delivery, DisplayPort, USB 3.2 Gen 1 (5Gbps) Hub, Gigabit Ethernet, 3.5mm headset port
- 85W POWER DELIVERY: This Thunderbolt 3 Docking Station will power and charge laptops & ultrabooks such as MacBook Pro 13 & 16, MacBook Air, HP, Lenovo ThinkPad, & Dell XPS using macOS and Windows.

- **COMPATIBILITY:** This docking station is compatible with Windows, macOS, and Ubuntu; Supports Thunderbolt or USB4 laptops; Dual Display on M1, M2, M3 Max/Pro, M4 Pro/Max MacBooks, and single display on base M-series MacBooks and iPad Pro M1 & later
- **FLEXIBLE THUNDERBOLT 3 PORT:** Thunderbolt 3 port replicator w/ a downstream TB3 port that supports 3 modes of operation: a second monitor, daisychain TB3 peripherals, or connect USB Type-C accessories
- **DAISYCHAIN UP TO 5 THUNDERBOLT 3 DEVICES:** Connect additional TB3 devices to this TB3 dock including monitors, external hard drive bays, card readers, or an external GPU; using the downstream TB3 port.

---

#### Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	Yes
Displays Supported	2
Bus Type	Thunderbolt 3
Industry Standards	Thunderbolt 3
	USB Battery Charging Specification Rev. 1.2
	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab
	USB 3.0 - Backward compatible with USB 2.0 and 1.1
Chipset ID	Intel - Alpine Ridge DSL6540
	Fresco - FL1100EX
	Texas Instruments - PCM2912A
	Intel - WGI210AT
	Texas Instruments - TPS65983

---

#### Performance

Maximum Data Transfer Rate	40 Gbps (Thunderbolt 3)
	10 Gbps (USB 3.1 Gen 2)
	5 Gbps (USB 3.0)
	2 Gbps (Ethernet; Full-Duplex)
Maximum Digital Resolutions	Single display - DisplayPort - 4096 x 2160p / 3840 x 2160p
	Single Display - Thunderbolt 3 USB-C - 4096 x 2160p / 3840 x

2160p

Dual displays - DisplayPort 4096 x 2160p / 3840 x 2160p and Thunderbolt 3 USB-C - 4096 x 2160p / 3840 x 2160p

Type and Rate	Thunderbolt 3 - 40 Gbit/s
UASP Support	Yes
Compatible Networks	10/100/1000 Mbps
Auto MDIX	Yes
Full Duplex Support	Yes

---

#### Connector(s)

Connector Type(s)	2 - Thunderbolt 3 USB-C (24-pin) (40Gbps)  1 - DisplayPort (20 pin)  1 - USB 3.2 Type-C (24 pin, Gen 1, 5Gbps)  1 - USB 3.2 Type-A (9 pin, Fast-Charge)  1 - USB Type-A (9 pin, 5 Gbps)  2 - 3.5 mm Mini-Jack (3 Position)  1 - RJ-45
-------------------	---

---

#### Software

OS Compatibility	Windows 7, 8, 8.1, 10, 11 macOS 10.12 - 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1
------------------	--

---

#### Special Notes / Requirements

System and Cable Requirements	Thunderbolt 3 equipped computer with a Thunderbolt 3 port.
	Your laptop's Thunderbolt 3 port must support USB Power Delivery 2.0 in order to power and charge your laptop.
Note	A 4K-capable display is required to achieve 4K x 2K resolution (4K is also known as 4K x 2K).  Certain monitors may be limited to 4K at 30Hz when connecting through DisplayPort. These monitors include the following models: Dell P2715Q, Viewsonic VX2475Smhl-4K, Philips 288P6LJEB, LG 31MU97C-B, Asus PB287Q (these models will need to be set to 4K at 30Hz).

When connecting a display to one of the Thunderbolt 3 USB-C ports, a USB-C video adapter might be required depending on the input of your display.

USB 3.0 is also known as USB 3.1 Gen 1; this connectivity standard offers speeds up to 5Gbps. USB 3.1 Gen 2 offers speeds up to 10Gbps.

MacBook Air and MacBook Pro systems using the new Apple M1 chip support only a single external display over the Thunderbolt 3 ports, even when connected to a Thunderbolt 3 docking station with more than one video output. This single monitor limitation does not affect Intel-based Macs with Thunderbolt 3.

---

**Power**

Power Source	AC Adapter Included
Power Delivery	85W
Input Voltage	100 - 240 AC
Input Current	2.5 A
Output Voltage	20V DC
Output Current	8.5 A
Plug Type	CP (OD:7.4/ID:5.1/CPD:0.6)
Power Consumption (In Watts)	170

---

**Environmental**

Operating Temperature	5C to 40C (41F to 104F)
Storage Temperature	-40C to 70C (-40F to 158F)
Humidity	5~95% RH (Non-condensing)

---

**Physical Characteristics**

Color	Gray and Black
Material	Aluminum and Plastic
Cable Length	20.5 in [520 mm]
Product Length	8.7 in [22.0 cm]
Product Width	3.1 in [8.0 cm]

Product Height 1.1 in [2.7 cm]

Weight of Product 15.9 oz [450.0 g]

---

**Packaging Information**

Package Quantity 1

Package Length 9.8 in [24.8 cm]

Package Width 5.7 in [14.6 cm]

Package Height 3.5 in [8.9 cm]

Shipping (Package) Weight 3.5 lb [1.6 kg]

---

**What's in the Box**

Included in Package 1 - docking station

1 - 1.7 ft. [520 mm] Thunderbolt 3 cable

1 - 6 ft. [1.8 m] USB-C to DP cable

1 - universal power adapter

2 - power cords (NA/JP, ANZ)

1 - instruction manual

---

**Warranty Information**

Warranty 3 Years

*\*Product appearance and specifications are subject to change without notice.*

