


MC16-0222SM

MMIC 2-22 GHz Directional Coupler

DEVICE OVERVIEW

General Description

MC16-0222SM is a MMIC 2-22 GHz Directional Coupler. Passive GaAs MMIC technology allows production of smaller constructions that replace larger form factor circuit board constructions. Tight fabrication tolerances result in less unit to unit variation than traditional coupler technologies, allowing for accurate simulations using the provided S3P file taken from measured production units. The MC16-0222SM is available as a 4 X 4 mm QFN package. Evaluation boards are also available.



[Download s-parameters here](#)


Features

- Broadband Performance
- Low VSWR
- High Directivity
- RoHS Compliant

Applications

N/A

Functional Block Diagram



Part Ordering Options

Part Number	Description	Package	Green Status	Product Lifecycle	Export Classification
MC16-0222SM	MMIC 2-22 GHz Directional Coupler	QFN	REACH RoHS	Released	EAR99
EVAL-MC16-0222	Evaluation Board, MMIC 2-22 GHz Directional Coupler	EVAL	REACH RoHS	Released	EAR99

Table Of Contents

■ Device Overview

General Description
 Features
 Applications
 Functional Block Diagram

■ Port Configuration and Functions

Port Diagram
 Port Functions

■ Revision History

■ Specifications

Absolute Maximum Ratings
 Package Information
 Electrical Specifications
 Typical Performance Plots

■ Mechanical Data

Outline Drawing

■ Footprint Image

■ Evaluation Board

Evaluation Board Outline Drawing


Revision History

Revision Code	Revision Date	Comment
-	2020-07-01	Initial Datasheet Release
A	2020-08-01	Updated Return Loss Plots
B	2025-02-12	Updated Power Handling
C	2025-11-21	Updated ESD Rating
D	2026-06-05	Corrected Unit of Power Handling Rating


Port Configuration and Functions

Port Diagram

A bottom-up view of the MC16-0222SM's SM package outline drawing is shown below.



Port Functions

Port	Function	Description	DC Equivalent Circuit
Pad	Ground	SM package ground path is provided through the ground paddle.	
Pin 1	Coupled	The coupled port is DC connected to a 50 Ω load.	
Pin 11	Output	The output port is DC short to the input port and open to ground.	
Pin 5	Input	The input port is DC short to the output port and open to ground.	

Specifications

Absolute Maximum Ratings

The Absolute Maximum Ratings indicate limits beyond which damage may occur to the device. If these limits are exceeded, the device may be inoperable or have a reduced lifetime.

Parameter	Maximum Rating	Unit
DC Current at any Port	60	mA
Maximum Operating Temperature	100	°C
Maximum Storage Temperature	125	°C
Minimum Operating Temperature	-55	°C
Minimum Storage Temperature	-65	°C
RF Power Handling	30	dBm

Package Information

Parameter	Details	Rating
ESD	250 to < 500 Volts	HBM Class 1A
Dimensions	-	4 x 4 mm
Moisture Sensitivity Level	-	MSL 1





Electrical Specifications

The electrical specifications apply at TA=+25°C in a 50Ω system. Min and Max limits are guaranteed at TA=+25°C. All measured data is taken from the eval board with de-embedding of the connectors and traces, but group delay may vary.

Parameter	Test Conditions	Minimum Frequency (GHz)	Maximum Frequency (GHz)	Min	Typ	Max	Unit
Directivity	-	12	22	-	15	-	dB
Directivity	-	2	12	14	23	-	dB
Direct Line Insertion Loss	DC-12	-	-	-	1.2	2.5	dB
Direct Line Insertion Loss	-	12	22	-	2	3.5	dB
Impedance	-	-	-	-	50	-	Ω
Mean Coupling	-	2	22	-	16	-	dB
VSWR	-	2	22	-	1.22	-	-

Typical Performance Plots


All measured data is taken from the eval board with de-embedding of the connectors and traces, but group delay may vary.



Mechanical Data

Outline Drawing

Download : [Outline 2D Drawing](#) | [Outline 3D Drawing](#) | [Outline 3D STP](#)




Notes:


- Substrate material is LCP.
- I/O Leads and Ground Paddle plating is (from base to finish):
 Ni: 0.5um MIN
 Pd: 0.02um MIN
 Au: 0.05um MAX
- All unconnected pins should be connected to PCB RF ground.

Footprint Image

Download : [Footprint Drawing](#)



Evaluation Board - Outline Drawing



DISCLAIMER

MARKI MICROWAVE, LLC., ("MARKI") PROVIDES TECHNICAL SPECIFICATIONS AND DATA (INCLUDING DATASHEETS), APPLICATION OR OTHER DESIGN ADVICE, WEB TOOLS, AND OTHER INFORMATION AND RESOURCES "AS IS" AND WITH ALL FAULTS. MARKI DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, WITHOUT LIMITATION, ANY IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT.

These resources are intended for developers skilled in the art designing with Marki products. You are solely responsible for (1) selecting the appropriate products for your application, (2) designing, validating, and testing your application, and (3) ensuring your application meets applicable standards and other requirements. Marki makes no guarantee regarding the suitability of its products for any particular purpose, nor does Marki assume any liability whatsoever arising out of your use or application of any Marki product.

Marki grants you permission to use these resources only for development of an application that uses Marki products. Other reproduction or use of these resources is strictly prohibited. No license is granted to any other Marki intellectual property or to any third-party intellectual property. Marki reserves the right to make changes to the product(s) or information contained herein without notice.

MARKI MICROWAVE, M wave logo, FastSwitch, and T3 MIXER are trademarks or registered trademarks of Marki Microwave, LLC. All other trademarks used are the property of their respective owners.

© 2020, 2025 - 2026, Marki Microwave, LLC