Features

- Ultra-low Q_G For High Efficiency
- Logic Level
- Light Weight
- No Wire Bond for Higher Reliability and Low Inductance
- Total Ionizing Dose LDR Immune
- Total Ionizing Dose HDR Immune
- Single Event Effect (SEE) Hardened
  - SEE immunity for LET of 83.2 MeV/(mg/cm^2) in Si with V_{DS} up to 100% of rated Breakdown
- Neutron
  - Maintains Pre-Rad specification for up to 4 x 10^{15} Neutrons/cm^2

Application

- Commercial Satellite EPS & Avionics
- Deep Space Probes
- High Speed Rad-Hard DC-DC Conversion
- Rad-Hard Motor Controllers
- Nuclear Facilities



JANSH2N7674UBC

Rad-Hard eGaN® 60 V, 1 A, 580 mΩ Surface Mount (UB)

Description


EPC Space Rad-Hard eGaN® power switching HEMTs have been specifically designed for critical applications in Space and other the high reliability environments. These devices have exceptionally high electron mobility and a low temperature coefficient resulting in very low $R_{DS(on)}$ values. The lateral structure of the die provides for very low gate charge (Q_G) and extremely fast switching times. These features enable faster power supply switching frequencies resulting in higher power densities, higher efficiencies and more compact packaging.

Thermal Characteristics

Symbol	Parameter-Conditions	Value	Units
$R_{\theta JA}$	Thermal Resistance Junction to Ambient (Note 3)	200	°C/W
$R_{\theta JC}$	Thermal Resistance Junction to Case	62.9	

I/O Pin Assignment *(Bottom View)*

Pin	Symbol	Description
1	G	Gate
2	D	Drain
3	S	Source
4	L	Lid Pad Connection



Absolute Maximum Rating *(T_C = 25°C unless otherwise noted)*

Symbol	Parameter-Conditions	Value	Units
V_{DS}	Drain to Source Voltage (Note 1)	60	V
	Drain-to-Source Voltage (up to 10,000 5 ms pulses at 150°C)	72	
I_D	Continuous Drain Current ID @ V_{GS} = 5 V, T_C = 25°C	1	A
I_{DM}	Single-Pulse Drain Current $t_{pulse} \leq 80$ µs	4	
V_{GS}	Gate to Source Voltage (Note 2)	+6 / -4	V
T_J , T_{STG}	Operating and Storage Junction Temperature Range	-55 to +150	°C
T_{sol}	Package Mounting Surface Temperature	260	
ESD	ESD Class	1A(ΔA)	
Weight	Device Weight	0.058	g

©2026 EPC SPACE

Electrical Characteristics (T_C = 25°C unless otherwise noted. Typical (TYP) values are for reference only.)

Parameter	Symbol	Test Conditions		MIN	TYP	MAX	Units
Maximum Drain to Source Voltage	V_{DSMAX}	V_{GS} = 0 V		60			V
Drain to Source Leakage	I_{DSS}	V_{DS} = 60 V, V_{GS} = 0 V	T_C = 25°C		0.17	100	µA
			T_C = 125°C		0.35	180	
Gate to Source Forward Leakage	I_{GSSF}	V_{GS} = 6 V	T_C = 25°C		2	600	
Gate to Source Reverse Leakage	I_{GSSR}	V_{GS} = -3 V	T_C = 25°C		0.27	100	
Gate to Source Threshold Voltage	$V_{GS(th)}$	V_{DS} = V_{GS} , I_D = 0.14 mA	T_C = 25°C	0.8	1.8	2.5	V
Gate to Source Threshold Voltage Temperature Coefficient	$\Delta V_{GS(th)}/\Delta T$	V_{DS} = V_{GS} , I_D = 0.14 mA	-55°C < T_A < 150°C		|2.34|		mV/°C
Drain to Source Resistance (Note 4)	$R_{DS(on)}$	I_D = 1 A, V_{GS} = 5 V	T_C = 25°C		340	580	mΩ
Source to Drain Forward Voltage	V_{SD}	I_S = 0.5 A, V_G = 0 V	T_C = 25°C		2.5	3.5	V

Dynamic Characteristics (T_C = 25°C unless otherwise noted. Typical (TYP) values are for reference only.)

Parameter	Symbol	Test Conditions	MIN	TYP	MAX	Units
Input Capacitance	C_{ISS}	V_{DS} = 30 V, V_{GS} = 0 V		18	28	pF
Output Capacitance	C_{OSS}			17	30	
Reverse transfer Capacitance	C_{RSS}			0.1	2	
Gate Resistance (Note 5)	R_G	f = 1 MHz, V_{DS} = V_{GS} = 0 V		12.6		Ω
Total Gate Charge (Note 6)	Q_G	V_{DS} = 30 V, I_D = 1 A		142	175	pC
Gate to Source Charge (Note 6)	Q_{GS}			20	46	
Gate to Drain Charge (Note 6)	Q_{GD}			30	40	
Output Charge (Note 5)	Q_{OSS}	V_{GS} = 0 V, V_{DS} = 30 V		764	1145	
Source to Drain Recovery Charge (Note 5)	Q_{RR}	I_D = 1 A, V_{DS} = 30 V		0		

©2026 EPC SPACE

Radiation Characteristics

EPC Space eGaN® HEMTs are tested according to MIL-STD-750 Method 1019 for total ionizing dose validation. Every manufacturing lot is tested for total ionizing dose of 1 Mrad of Gamma radiation exposure with an in-situ bias for the following conditions:

ON | V_{GS} = 5 V
NO BIAS | V_{DS} = V_{GS} = 0 V
OFF | V_{DS} = 80% B_{VDSS}

Electrical Characteristics up to 1000 krads *(T_C = 25°C unless otherwise noted. Typical (TYP) values are for reference only.)*

Parameter	Symbol	Test Conditions	MIN	TYP	MAX	Units
Maximum Drain to Source Voltage	V_{DSMAX}	V_{GS} = 0 V	60			V
Gate to Source Threshold Voltage	$V_{GS(th)}$	V_{DS} = V_{GS} , I_D = 0.14 mA	0.8	1.8	2.5	
Drain to Source Leakage	I_{DSS}	V_{DS} = 60 V, V_{GS} = 0 V		0.35	100	µA
Gate to Source Forward Leakage	I_{GSSF}	V_{GS} = 6 V		2	600	
Gate to Source Reverse Leakage	I_{GSSR}	V_{GS} = -3 V		0.27	100	
Drain to Source Resistance (Note 4)	$R_{DS(on)}$	I_D = 1 A, V_{GS} = 5 V		365	580	mΩ

Typical Single Event Effect Safe Operating Area

Note: All Radiation Single Event Effects testing are performed in heavy ion environments such as the K-500 Cyclotron at Texas A&M.

Test	Environment				V_{DS} Voltage (V)	
	Ion	LET MeV(mg/cm^2) in Si (+/-5%)	Range µm (+/- 7.5%)	Energy MeV (+/-10%)	V_{GS} = 0 V	V_{GS} = -4V
See SOA	Xe	63.6	71.3	963	60	60
	Au	83.2	121.4	2256	60	60




Figure 1. Typical Single Event Effect Safe Operating Area




Figure 2. Typical Gate-Source Leakage Current vs. Ambient Temperature




Figure 3: Typical Drain-Source Leakage Current vs. Ambient Temperature




Figure 4. Typical Output Characteristics at 25°C




Figure 5. Typical Output Characteristics at 125°C




Figure 6. Typical Transfer Characteristics




Figure 7. Reverse Drain-Source Characteristics

©2026 EPC SPACE




Figure 8. $R_{DS(on)}$ vs. V_{GS} for Various Drain Currents




Figure 9. $R_{DS(on)}$ vs. V_{GS} for Various Temperatures




Figure 10. Normalized On-State Resistance vs. Temperature




Figure 11. Normalized Threshold Voltage vs. Temperature




Figure 12. Typical Capacitance




Figure 13. Typical Output Charge and C_{OSS} Stored Energy

©2026 EPC SPACE




Figure 14. Gate Charge




Figure 15. Safe Operating Area





Figure 16. Transient Thermal Impedance, Junction to Case


Package Outline and Dimensions



Symbol	IN			MM		
	MIN	MAX	REF	MIN	MAX	REF
A	0.115	0.127		2.92	3.23	
B	0.095	0.107		2.41	2.72	
C			0.107			2.72
D			0.09			2.29
E	0.016	0.024		0.41	0.61	
F	0.035	0.04		0.89	1.02	
G	0.071	0.079		1.8	2	
H	0.064	0.083		1.63	2.11	
J	0.024	0.036		0.61	0.91	
K			0.022			0.56
L			0.008			0.2
M	0.015	0.025		0.38	0.64	
N			0.012			0.3
P	0.055	0.065		1.4	1.65	


Standard Terminal Pad finish is a solder alloy of 63%Sn 37%Pb

Package Connections



NOTE: SS pin is connected directly to source of internal die.

UB Footprint for Printed Circuit Board Design



Symbol	IN	MM	Note
	NOM	NOM	
A	0.07	1.78	
B	0.052	1.32	
C	0.038	0.97	
D	0.075	1.91	
E	0.036	0.91	
F	0.028	0.71	

Suggested footprint:
NOM. DIM = .003 in [0.08 mm] swell on average

©2026 EPC SPACE

Notes

Note 1. Never exceed the absolute maximum V_{DS} of the device otherwise permanent damage/destruction may result.

Note 2. Never exceed the absolute maximum V_{GS} of the device otherwise permanent damage/destruction may result. We recommend a V_{GS} of 5V for optimum operation across life and radiation.

Note 3. $R_{\theta JA}$ measured with LCC3 package mounted to double-sided PCB, 0.063" thickness with 1.0 square inches of copper area on the top (mounting side) and a flood etch (3 square inches) on the bottom side.

Note 4. Measured using four wire (Kelvin) sensing and pulse measurement techniques. Measurement pulse width is 80 µs and duty cycle is 1%, maximum.

Note 5. Guaranteed by design/device construction. Not tested.

Note 6. The gate charge parameters are measured based on the MIL-STD-750.3471 Condition B. A high speed constant gate current (I_{const}) is provided to the Gate of the DUT during the time that the ground switch (G_S) is OFF (t_{off}). The DUT is switched ON and OFF using ground-sensed switch G_S. The gate current is adjusted to yield the desired charge per unit time (I_{const} · time per division) on the measuring oscilloscope. The G_S pulse drive ON time (t_{on}) is adjusted for the desired observability of the gate-source voltage (V_{GS}) waveform. The maximum duty cycle of the ground switch (t_{off} /t_{on}) should be set to 1% maximum. Please note that all gate-related signals are referenced to the "Source Sense" pin on the package. At all times during the measurement, the maximum gate-source voltage is clamped to 5 V_{DC}.

©2026 EPC SPACE

Disclaimers

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE. EPC Space Corporation, its affiliates, agents, employees, and all persons acting on its or their behalf (collectively, "EPC Space"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product. EPC Space makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose. To the maximum extent permitted by applicable law, EPC Space disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability. Statements regarding the suitability of products for certain types of applications are based on EPC Space market knowledge of typical requirements that are often placed on similar technologies in generic applications. Product specifications do not expand or otherwise modify EPC Space terms and conditions of purchase, including but not limited to the warranty expressed therein. Except as expressly indicated in writing, EPC Space products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the EPC Space product could result in personal injury or death. Customers using EPC Space products not expressly indicated for use in such applications do so at their own risk. Please contact authorized EPC Space personnel to obtain written terms and conditions regarding products designed for such applications. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of EPC Space. Product names and markings noted herein may be trademarks of their respective owners.

Export Administration Regulations (EAR)

The products described in this datasheet are subject to the U.S. Export Administration Regulations (EAR), 15 C.F.R. Pts 730-774, and are classified in ECCN 9A515.e. These products may not be exported, reexported, or transferred (in country) to any foreign country, or foreign entity, by any means, except in accordance with the requirements of such regulations.

Patents

EPC Corporation and EPC Space hold numerous worldwide patents. Any that apply to the product(s) listed in this document are identified by markings on the product(s) or on internal components of the product(s) in accordance with local patent laws.

eGaN® is a registered trademark of Efficient Power Conversion Corporation, Inc. Data and specification subject to change without notice.

Information subject to change without notice.

Change Log

Status	Version	Date	Remark
1.1	Preliminary datasheet	24 April 2026	Preliminary Release
1.0	Preliminary datasheet	24 January 2026	Preliminary Release

©2026 EPC SPACE