

Special



*Image for illustrative purpose only*

## Summary

[Request a quote](#)

00and01Coaxial en

Nb of contacts Coax	1
Locking system	Push-pull
Size	00
Series	00 - NIM-CAMAC

# Technical details

## Electrical Configuration

Nb of contacts Coax	1
Contact Termination Coax - Conductor fixing	Solder
Insert configuration value	0.25 - 1 Coax (50 Ohm)
Insulator	T: PTFE
Rated current	4 A
Impedance	50 Ohms
VSWR	$1.09 + 0.11 * f/\text{GHz}$
Vtest	2100 V (AC), 3000 V (DC)
Contact Dia.	0.7 mm (0.03in)

## Form & Material

Shell style / Model id	APF - Adapter from LEMO plug to CINCH receptacle
Housing material	Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Weight	7.93 g

## Environment

Environmental sealing (IP rating)	IP50
Endurance	>1000 mating cycles
F ret (min)	100 N

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
------------------------------	--

## Drawings



[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/apf-00-250-dtar.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/apf-00-250-dtar.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

## Dimensions

	<b>A</b>	<b>L</b>	<b>M</b>
mm.	6.4	43	34.5
in.	0.25	1.69	1.36

[https://www.lemo.com/int\\_en/solutions/specialties/00-nim-camac/apf-00-250-dtar.html](https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/apf-00-250-dtar.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.