

Standard*Image for illustrative purpose only*

Summary

[Request a quote](#)[BKT series](#)[Customer Drawing](#)

Size

3B

Series

B - Indoor keyed

Technical details

Electrical Configuration

Footprint IPC Class3 compatibility	No
------------------------------------	----

Form & Material

Shell style / Model id	BFG - Cap for plug
Housing material	POM (Polyoxymethylene) shell without treatment, silicone gasket
Keying	G: 1 key (alpha=0, plug: male contacts, receptacle: female contacts)
Weight	3.15 g

Environment

Technical domain	Audio Video, Energy and Industrial, Medical, Semiconductor, Specialties and Other, Test and Measurement, Transportation, Aerospace and UAV
Environmental sealing (IP rating)	IP50
Temperature range	-50°C / +100°C
Climatic Category	55/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]

https://www.lemo.com/int_en/solutions/originals/b-indoor-keyed/bfg-3b-100-pcsg.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.