


ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	C	ECO-15414	01/16/2026	DMAY	DGUST



NOTES:

1. VOLTAGE RATING:
DIELECTRIC VOLTAGE WITHSTAND TEST: 1500V / 1 Sec
CONDUCTOR RESISTANCE $\leq 8.88\Omega/1000M$
VOLTAGE RATING AC 300V
2. CABLE MARKING:
(UL) E135710-F5 SJT 3x14AWG 105°C 300V VW-1
c(UL)SJT 3x2.08 mm² (14AWG) 105°C 300V FT2
3. OPTIONAL LABELS:
OPTIONAL LABEL(S) MAY INCLUDE
UL, CURRENT AND/OR WARNING
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

TOLERANCES:
 $X = \pm 0.2 [0.5]$ FRACTIONS
 $XX = \pm 0.02 [0.5]$ $\pm 1/32$
 $XXX = \pm .005 [0.13]$ ANGLES $\pm 1^\circ$

CABLE LENGTH TOLERANCES:
 $\leq 12 [305] = \pm 1 [25] / -0$
 $> 12 [305] \leq 60 [1524] = \pm 2 [51] / -0$
 $> 60 [1524] \leq 120 [3048] = \pm 4 [102] / -0$
 $> 120 [3048] \leq 300 [7620] = \pm 6 [152] / -0$
 $> 300 [7620] = \pm 5\% / -0$

ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE
UN-DIMENSIONED/NON-CRITICAL FEATURES
MAY VARY IN SIZE AND LOCATION
COLORS MAY VARY

L-com
an INFINITE[®] brand

Website: www.L-com.com
Phone: 1.800.341.5266 | 1.978.682.6936



INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

SCALE SHEET
NONE 1 OF 1

DESCRIPTION
C14 - 2C13 SPLIT POWER CORD, 15A, 250V

ITEM NO.	REV
C14-C132-15	C