

Fiber Optic Transceiver, SFP, CWDM, ZX SMF 80KM,
1000Base DDM, Brocade/Foundry Compliant



FXC-SFP-CxxZX-1G-BFO

Features

- Operating Data Rate up to 1.25 Gbps
- Distance Range 80KM
- Pluggable SFP Duplex LC Connectors
- Standard and Industrial Operating Temperature
- Compliant with Brocade/Foundry Specification

Applications

- Telecom (Service Providers)
- Datacom
- Enterprise Networks
- Government
- Fiber to the home / business

Description

The L-com FXC-SFP-CxxZX-1G-BFO series are SFP transceivers, supporting 1G Ethernet data rates. The SFP CWDM series transceivers have CWDM transmitters, with operating wavelengths between 1470 nm to 1610 nm. The L-com FXC-SFP-CxxZX-1G-BFO series support 80KM distance and are compliant with Brocade/Foundry system level specifications. The L-com FXC-SFP-CxxZX-1G-BFO series feature digital diagnostics for performance monitoring of the transceivers. The L-com FXC-SFP-CxxZX-1G-BFO series are one of thousands of fiber optic connectivity products available from L-com's in-stock inventory and ready to ship. Contact our knowledgeable technical support and sales staff with your questions on fiber optic connectivity or other L-com products.

Configuration

Data Rate	1.25 Gbps
Form Factor	SFP
Connector	LC
Connector Mode	Duplex
Mode	Single Mode
Distance	80 km
Mfg Platform Compatibility	Brocade/Foundry

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Power Supply Voltage	3.15	3.3	3.45	V
Power Supply Current			300	mA
Module Total Power			1	W

Optical Specifications

Description	Minimum	Typical	Maximum	Units
TX Center Wavelength*	$\lambda_c - 6$	λ_c	$\lambda_c + 7.5$	nm
TX Data Rate	1.06		1.25	Gbps
TX Average Output Power	0		5	dBm
TX Extinction Ratio	8.2			dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications:
[FXC-SFP-CxxZX-1G-BFO](#)

Fiber Optic Transceiver, SFP, CWDM, ZX SMF 80KM,
1000Base DDM, Brocade/Foundry Compliant



FXC-SFP-CxxZX-1G-BFO

RX Center Wavelength	1260	1620	nm
RX Receiver Sensitivity		-24	dBm
RX Receiver Overload	-3		dBm

*See table below

Wavelength Channel No.

ITU Channel No.	Wavelength	Latch color by wavelength
(xx)	nm	
47	1471	
49	1491	
51	1511	
53	1531	
55	1551	
57	1571	
59	1591	
61	1611	

Environmental Specifications

Temperature

Operating Range

Storage Range

0 to +70 deg C

-40 to +85 deg C

Fiber Optic Transceiver, SFP, CWDM, ZX SMF 80KM,
1000Base DDM, Brocade/Foundry Compliant



FXC-SFP-CxxZX-1G-BFO


Notes:

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Small Form-factor Pluggable (SFP) Transceiver MultiSource Agreement (MSA)



Fiber Optic Transceiver, SFP, CWDM, ZX SMF 80KM,
1000Base DDM, Brocade/Foundry Compliant



FXC-SFP-CxxZX-1G-BFO




Figure 1. Diagram of Host Board Connector Block Pin Numbers and Names

Fiber Optic Transceiver, SFP, CWDM, ZX SMF 80KM, 1000Base DDM, Brocade/Foundry Compliant from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

