

Lead Free Bend Relief 3-Slot TRB Plug to Plug for
78 Ohm M17/176-00002-LC, 48" Cable



LC3MSA00441-48

Configuration

- Connector 1: TRB 3-Slot Plug
- Connector 2: TRB 3-Slot Plug
- Cable Type: M17/176-00002-LC

Features

- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

Applications

- Vehicle High Temperature
- Data
- MIL-STD-1553

Description

L-com's LC3MSA00441-48 is a lead free bend relief 3-Slot TRB plug to plug for 78 Ohm M17/176-00002-LC, 48" cable and ships same-day. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com TRB 3-Slot to TRB 3-Slot cable assembly has a plug to plug gender configuration with 78 Ohm flexible M17/176-00002-LC series coax and operates to 10 MHz.

Custom versions of this TRB 3-Slot plug to TRB 3-Slot plug cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LC3MSA00441-48 L-com Lead Free Bend Relief 3-Slot TRB Plug to Plug for 78 Ohm M17/176-00002-LC, 48" Cable data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	MHz
Capacitance		24 [78.74]		pF/ft [pF/m]
Operating Voltage (AC)			750,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	5	7	10	MHz
Insertion Loss (Typ.)	0.256	0.284	0.312	0.34	0.38	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Lead Free Bend Relief 3-Slot TRB Plug to Plug for
78 Ohm M17/176-00002-LC, 48" Cable



LC3MSA00441-48

Mechanical Specifications

Cable Assembly

Length*	48 in [121.92 cm]
Weight	0.172 lbs [78.02 g]

Cable

Cable Type	M17/176-00002-LC
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Shield Layer 1	Silver Plated Copper
Jacket Material	PFA, Blue
One Time Minimum Bend Radius	1.5 in [38.1 mm]

Connectors

Description	Connector 1	Connector 2
Type	TRB 3-Slot Plug	TRB 3-Slot Plug
Impedance	78 Ohms	78 Ohms
Contact Material and Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Specification	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Conductor Plating Specification	30 micro inches	30 micro inches
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	ASTM-B-733	ASTM-B-733

Environmental Specifications

Temperature

Operating Range -55 to +200 deg C

Compliance Certifications

(see [product page](#) for current document)

Plotted and Other Data

Notes:


Lead Free Bend Relief 3-Slot TRB Plug to Plug for
78 Ohm M17/176-00002-LC, 48" Cable



LC3MSA00441-48

How to Order

Part Number Configuration:



Example: LC3MSA00441-12 = 12 inches long cable
LC3MSA00441-100cm = 100 cm long cable

Lead Free Bend Relief 3-Slot TRB Plug to Plug for 78 Ohm M17/176-00002-LC, 48" Cable from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

Lead Free Bend Relief 3-Slot TRB Plug to Plug for 78 Ohm M17/176-00002-LC, 48" Cable

L-com CAD Drawing

LEAD FREE SOLDER

ZONE	RE
	A

— LENGTH —

LABEL
SEE NOTE 1

www.l-com.com
LCXXXXX

— M17/176-00002, 78 OHM TWINAX CABLE
JACKET: FEP, BLUE
NOM. DIA.: 129" [3.28]

The diagram illustrates a TRB 3-Slot Plug assembly. At the bottom, a black cylindrical component labeled '2X TRB 3-SLOT PLUG WITH BEND RELIEF' is shown. Above it, a white cylindrical component labeled '2X BEND RELIEF' is attached. At the very top, a white rectangular component labeled 'M11 JAC NO' is shown. Arrows point from the text labels to their respective parts: '2X TRB 3-SLOT PLUG' points to the black base, '2X BEND RELIEF' points to the white cylindrical part, and 'M11 JAC NO' points to the top white component.

The diagram illustrates a wiring map for a central terminal block. A vertical line on the left is labeled "SHIELD". Three wires, labeled "WHITE", "BLUE", and a ground wire (represented by a circle with two dots), are connected to a central terminal block. The "WHITE" and "BLUE" wires are connected to the same terminal, while the ground wire is connected to a separate terminal. Dashed circles around the central block indicate the connection points.

NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
2. CABLE ASSEMBLY LENGTH DETERMINED BY PN AS ILLUSTRATED
C3MSA00441-XX (-XXX = OA) IN INCHES)
- 3.

EU RoHS DIRECTIVE (MOST RECENT RELEASED VERSION)
REGULATORY COMPLIANCE

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN

DESCRIPTION		TOLERANCES PER ASME Y14.5	
SCALE	SHEET	SCALE	SHEET
1 OF 1	1 OF 1	1 OF 1	1 OF 1
1.800.341.5266 1.978.682.6936	Website: www.l-com.com	1.800.341.5266 1.978.682.6936	Website: www.l-com.com

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

REV A
LC3MSA00441
ITEM NO.
DRAWN BY
CAGE CODE
SIZE

101W1110-0000Z CRADLE