

2W/20 dB RF fixed attenuator, TNC Male to
TNC Female, Brass Body, DC to 3GHz



LCAT7609-20

Features

- DC to 3 GHz Range
- Attenuation 20 $\pm$ 0.5 dB
- 2 Watts (CW) Power
- VSWR <1.25:1

Applications

- Precision Measurements
- Production Systems
- Instrumentation
- Prototyping and Characterization

Description

L-com carries a wide range of fixed attenuators with a broad selection of attenuation levels, frequency ranges, and power dissipation ranges. RF microwave attenuators (also known as RF pads) lower the amplitude of a signal (attenuate) a known amount and can be used in a wide variety of applications. These attenuators pads are used when a signal needs to be reduced to protect measurement equipment or other circuitry, to extend the range of power meters and amplifiers, and to impedance match circuits by reducing the VSWR seen by adjacent components. RF attenuators can prevent signal overload in amplifiers, receivers and detectors, adjusting the signal level to a range that is optimal.

Few RF components are as commonly used as fixed coaxial attenuators, and L-com carries one of the largest in-stock varieties and ships them same day. The 20 dB Fixed Attenuators LCAT7609-20 is rated to 2 Watts and operates from DC to 3 GHz. The versatile coaxial package uses TNC male to TNC female connectors.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
Impedance		50		Ohms
Nominal Attenuation		20		dB
Attenuation Accuracy		0.5		dB
VSWR			1.25:1	
Input Power, CW			2	Watts

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency Range	DC to 2	2 to 3				GHz
VSWR, Max	1.15:1	1.25:1				

Mechanical Specifications

Size

Length	2.087 in [53.01 mm]
Width/Diameter	0.63 in [16 mm]
Height	0.63 in [16 mm]
Weight	0.085 lbs [38.56 g]
Body Material and Plating	Brass, Copper-Tin-Zinc Alloy

Configuration

Design	Fixed, Bidirectional
--------	----------------------

2W/20 dB RF fixed attenuator, TNC Male to
TNC Female, Brass Body, DC to 3GHz



LCAT7609-20

Connectors

Description	Connector 1	Connector 2
Type	TNC Male	TNC Female
Contact Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Dielectric Type	Teflon	Teflon
Body Material and Plating	Brass, Copper-Tin-Zinc Alloy	Brass, Copper-Tin-Zinc Alloy

Environmental Specifications

Temperature

Operating Range -50 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Typical Performance Data

2W/20 dB RF fixed attenuator, TNC Male to TNC Female, Brass Body, DC to 3GHz from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

URL: <https://www.l-com.com/2w-20-db-rf-fixed-attenuator-tnc-male-tnc-female-brass-body-dc-3ghz-lcat7609-20-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

2W/20 dB RF fixed attenuator, TNC Male to TNC Female, Brass Body, DC to 3GHz

