

N Male to SMA Male Cable Assembly using RG58 Coax, 1.5 FT

## LCCA30665-FT1.5



### Configuration


- Connector 1: N Male
- Connector 2: SMA Male
- Cable Type: RG58

### Features

- 50 Ohm RF (Radio Frequency) Transmission
- RG58 stranded center conductor enhances flexibility
- Same day shipping available
- Heat shrink strain relief for a highly durable RF cable assembly

### Applications

- RFID systems up to 1 GHz
- General Purpose Test and Measurements
- Wireless Infrastructure
- GPS Timing and telematics



### Description

L-com's LCCA30665-FT1.5 is a N male to SMA male cable assembly using RG58 coax, 1.5 FT and ships same-day. The RG58 coax of this N cable uses the PTFE dielectric with a VoP of 69.5%. These flexible RF cable assemblies are ideal for applications where flexure is required. Our L-com N to SMA cable assembly has a male to male gender configuration with flexible RG58 series coax and operates to 1 GHz. The shielding of this N cable is comprised of tinned copper braid.

Custom versions of this N male to N male cable, along with the rest of L-com's other RF assemblies, can also be built and shipped same day. Other available RF cable assembly value added services from L-com include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly. Contact a sales representative for testing or custom RF cable quotes. Part number LCCA30665-FT1.5 L-com N Male to SMA Male Cable Assembly using RG58 Coax, 1.5 FT data sheet PDF includes details of the RF product specifications, CAD drawing(s) and dimensions below.

### Electrical Specifications

| Description     | Minimum | Typical | Maximum | Units |
|-----------------|---------|---------|---------|-------|
| Frequency Range | DC      |         | 1,000   | MHz   |
| VSWR            |         |         | 1.4:1   |       |

N Male to SMA Male Cable Assembly using RG58 Coax, 1.5 FT



## LCCA30665-FT1.5

|                         |              |              |
|-------------------------|--------------|--------------|
| Velocity of Propagation | 69.5         | %            |
| Capacitance             | 16.1 [52.82] | pF/ft [pF/m] |

### Specifications by Frequency

| Description           | F1   | F2   | F3   | F4   | F5    | Units |
|-----------------------|------|------|------|------|-------|-------|
| Frequency             | 50   | 100  | 200  | 400  | 1,000 | MHz   |
| Insertion Loss (Typ.) | 0.24 | 0.27 | 0.31 | 0.37 | 0.52  | dB    |

#### Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable and connectors used in this assembly.  
The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

### Mechanical Specifications

#### Cable Assembly

Length 18 in [457.2 mm]

#### Cable

Cable Type RG58  
Impedance 50 Ohms  
Inner Conductor Type Stranded  
Inner Conductor Material and Plating Copper, Silver  
Dielectric Type PTFE  
Number of Shields 1  
Shield Layer 1 Tinned Copper Braid  
Jacket Material PVC, Black  
Jacket Diameter 0.197 in [5 mm]

Repeated Minimum Bend Radius 2 in [50.8 mm]

### Connectors

| Description                       | Connector 1   | Connector 2           |
|-----------------------------------|---------------|-----------------------|
| Type                              | N Male        | SMA Male              |
| Impedance                         | 50 Ohms       | 50 Ohms               |
| Contact Material and Plating      | Brass, Gold   | Phosphor Bronze, Gold |
| Dielectric Type                   | PTFE          | PTFE                  |
| Body Material and Plating         | Brass, Nickel | Brass, Nickel         |
| Coupling Nut Material and Plating | Brass, Nickel | Brass, Nickel         |

N Male to SMA Male Cable Assembly using RG58 Coax, 1.5 FT



## LCCA30665-FT1.5

### Environmental Specifications

#### Temperature

Operating Range

-20 to +80 deg C

**Compliance Certifications** (see [product page](#) for current document)

### Plotted and Other Data

Notes:

### How to Order

Part Number Configuration:

**LCCA30665**

**- xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: LCCA30665-12 = 12 inches long cable  
LCCA30665-100cm = 100 cm long cable

N Male to SMA Male Cable Assembly using RG58 Coax, 1.5 FT from L-com has same day shipment for domestic and International orders. L-com is a leading manufacturer of wired and wireless connectivity products and committed to in-stock availability and same day shipping. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

